PHILIPS Lighting



Maxos LED Performer

4MX900 491 LED50S/840 PSD WB WH

Maxos LED Performer, Generation 3, LED module, system flux 5000 lm, 840 neutral white, Power supply unit with DALI interface, Wide beam, White

Customers want to save energy and reduce cost compared to what they are used to with conventional lighting. At the same time, excellent lighting conditions are needed: in industrial environments, to guarantee safety and productivity; and in retail environments, to make the merchandise stand out and attract shoppers. Maxos LED Performer is an extremely flexible solution that delivers low energy consumption and excellent beam shaping at an attractive investment level.

Product data

General Information	
Lamp family code	LED50S [LED module, system flux 5000
	lm]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically
	there is no relevant difference in lumen
	maintenance between B50 and for
	example B10. Therefore, the median useful
	life (B50) value also represents the B10
	value.
Service tag	Yes
Product family code	4MX900 [Maxos LED Performer]

Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	5,000 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	155 lm/W
Color rendering index (CRI)	≥80
Number of light sources	1

Maxos LED Performer

	120 degree(c)
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	90°
Unified glare rating CEN	Not applicable
Operating and Electrical	
Operating and Electrical	220 += 240 V
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.192 ms
Power Consumption	32.2 W
Power Factor (Fraction)	0.9
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	29
Temperature	
Temperature	-20 to +40 °C
Ambient temperature range	-20 t0 +40 C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,479 mm
Overall width	87 mm
Overall height	82 mm
Dimensions (Height x Width x Depth)	82 x 87 x 1479 mm
Approval and Application	
Ingress protection code	IP40 [Wire-protected]

Mech. impact protection code	IK02 [0.2 J standard]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to
	EN62778

Initial Performance (IEC Compliant)
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM <3.5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful	5 %
life 50000 h	
Control gear failure rate at median useful	10 %
life 100000 h	
Lumen maintenance at median useful life*	L90
50000 h	
Lumen maintenance at median useful life*	L80
100000 h	

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable


Product Data	
Order product name	4MX900 491 LED50S/840 PSD WB WH
Full product name	4MX900 491 LED50S/840 PSD WB WH
Full product code	403073266628799
Order code	66628799
Material Nr. (12NC)	910629144826
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	4030732666287
Numerator - Packs per outer box	2
EAN/UPC - Case	4030732264452

Ingress protection code

IP40 [Wire-protected]

Maxos LED Performer

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, August 31 - data subject to change