



Metronomis LED Fluid

BDS670 GRN15-3S/830 PSU II MDS CIR C450

Metronomis LED - LED GreenLine 1500 lm - Power supply unit - Metronomis distribution symmetrical - Prismatic circle effect element

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

Product data

General Information			
Number of light sources	1 [1 pc]	Luminaire light beam spread	17°
Lamp family code	GRN15 [LED GreenLine 1500 lm]	Embedded control	No [-]
Lamp version	2S [2nd generation, screw fixation]	Light regulation	-
Light source color	830 warm white	Electrical circuit protection	-
Light source replaceable	Yes	Connection	SCREW [Screw connector]
Number of gear units	1 unit	Cable	Cable 450 mm without plug
Driver/power unit/transformer	PSU [Power supply unit]	Protection class IEC	Safety class II (II)
Driver included	Yes	Coating	-
Optical element	CIR [Prismatic circle effect element]	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Optical cover/lens type	PC [Polycarbonate bowl/cover]	Flammability mark	NO [-]
		CE mark	CE mark

Metronomis LED Fluid

ENEC mark	ENEC mark
Warranty period	5 years
Optic type outdoor	Metronomis distribution symmetrical
Photozell	No [-]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Number of products on MCB of 16 A type B	20
RoHS mark	RoHS mark
Light source engine type	LED
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection device, optics, front cover and mechanical parts
Product family code	BDS670 [Metronomis LED]

Light Technical

Standard deviation color matching	5
Upward light output ratio	5
Standard tilt angle posttop	-
Standard tilt angle side entry	-

Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Factor (Min)	0.92

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminum
Mounting device	60 [Spigot for diameter 60 mm]

Optical cover/lens shape	-
Optical cover/lens finish	-
Overall height	990 mm
Overall diameter	560 mm
Effective projected area	0.4396 m ²
Color	Gray
Dimensions (Height x Width x Depth)	990 x NaN x NaN mm (39 x NaN x NaN in)

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level kV

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1022 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	60 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.430, 0.300) SDCM <5
Initial input power	12.8 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions


Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C

Product Data

Full product code	871829188500900
Order product name	BDS670 GRN15-3S/830 PSU II MDS CIR C450
EAN/UPC - Product	8718291885009
Order code	88500900
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910925437972
Net Weight (Piece)	17.143 kg

Metronomis LED Fluid

Dimensional drawing



Metronomis LED BDS650-670

