



Metronomis LED Fluid

BDS670 GRN15-3S/830 PSU II MDS STAR C450

Metronomis LED, LED GreenLine 1500 lm, Power supply unit (On/Off), Metronomis distribution symmetrical

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

Product data

General Information		
Lamp family code	GRN15 [LED GreenLine 1500 lm]	
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Photocell	-	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source engine type		LED
Product family code		BDS670 [Metronomis LED]
Lighting Technology		LED
Value ladder		Specification
Embedded control		-
CE mark		Yes
Warranty period		5 years
Flammability mark		-
ENEC mark		ENEC mark
Glow-wire test		Temperature 650 °C, duration 5 s

Metronomis LED Fluid

EU RoHS compliant	Yes
-------------------	-----

Light Technical

Standard deviation color matching	5
Upward light output ratio	5
Luminous Flux	958 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	56 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	17°
Optic type outdoor	Metronomis distribution symmetrical

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	12.8 W
Power Factor (Fraction)	0.92
Connection	Screw connector
Cable	Cable 0.45 m without plug
Number of products on MCB of 16 A type B	20

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum

Housing Color	Grey
Mounting device	Spigot for diameter 60 mm
Optical cover shape	-
Optical cover finish	-
Overall height	990 mm
Overall diameter	560 mm
Effective projected area	0.4396 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.430, 0.300) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BDS670 GRN15-3S/830 PSU II MDS STAR C450
Full product name	BDS670 GRN15-3S/830 PSU II MDS STAR C450
Full product code	871829188502300
Order code	88502300
Material Nr. (12NC)	910925437974
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291885023
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291885023

Metronomis LED Fluid

Dimensional drawing

