



# Metronomis LED Fluid

## BDS670 GRN15-3S/830 PSR-CLO II MDM 60

Metronomis LED, LED GreenLine 1500 lm, Power supply unit regulating with constant light output, Metronomis distribution medium, Spigot for diameter 60 mm

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

### Product data

General Information		B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Lamp family code	GRN15 [LED GreenLine 1500 lm]		
Light source replaceable	Yes		
Number of gear units	1 unit		
Driver included	Yes		
Photocell	-		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example		
		Light source engine type	LED
		Service tag	Yes
		Product family code	BDS670 [Metronomis LED]
		Lighting Technology	LED
		Value ladder	Specification
		Embedded control	-

# Metronomis LED Fluid

CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Standard deviation color matching	5
Upward light output ratio	5
Luminous Flux	1,396 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color rendering index (CRI)	>80
Number of light sources	1
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	48° x 66°
Optic type outdoor	Metronomis distribution medium

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	9.984 W
Average CLO power consumption	11.392 W
End CLO power consumption	12.8 W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	12.8 W
Power Factor (Fraction)	0.92
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	20

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Constant light output	Yes

## Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 mm
Optical cover shape	-
Optical cover finish	-
Overall height	990 mm
Overall diameter	560 mm
Effective projected area	0.4396 m²

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.430, 0.300) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

## Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

## Product Data

Order product name	BDS670 GRN15-3S/830 PSR-CLO II MDM 60
Full product name	BDS670 GRN15-3S/830 PSR-CLO II MDM 60
Full product code	871829188510800
Order code	88510800
Material Nr. (12NC)	910925437982
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291885108
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291885108

## Metronomis LED Fluid

### Dimensional drawing

