



Metronomis LED Fluid

BDS670 GRN30-3S/830 PSR-CLO II MDM 60

Metronomis LED - LED GreenLine 3000 lm - Power supply unit regulating with constant light output - Metronomis distribution medium - Spigot for diameter 60 mm

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

Product data

General Information			
Number of light sources	1 [1 pc]	Optical cover/lens type	PC [Polycarbonate bowl/cover]
Lamp family code	GRN30 [LED GreenLine 3000 lm]	Luminaire light beam spread	48° x 66°
Lamp version	2S [2nd generation, screw fixation]	Embedded control	No [-]
Light source color	830 warm white	Light regulation	-
Light source replaceable	Yes	Electrical circuit protection	-
Number of gear units	1 unit	Connection	SCREW [Screw connector]
Driver/power unit/transformer	PSR-CLO [Power supply unit regulating with constant light output]	Cable	-
Driver included	Yes	Protection class IEC	Safety class II (II)
Optical element	No [-]	Coating	-
		Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
		Flammability mark	NO [-]

Metronomis LED Fluid

CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Optic type outdoor	Metronomis distribution medium
Photozell	No [-]
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	Yes
Number of products on MCB of 16 A type B	20
EU RoHS compliant	Yes
Light source engine type	LED
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection device, optics, front cover and mechanical parts
Product family code	BDS670 [Metronomis LED]

Light Technical

Standard deviation color matching	5
Upward light output ratio	5
Standard tilt angle posttop	-
Standard tilt angle side entry	-

Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50 to 60 Hz
Initial CLO power consumption	19.656 W
Average CLO power consumption	22.428 W
End CLO power consumption	25.2 W
Inrush current	22 A
Inrush time	0.29 ms
Power Factor (Min)	0.98

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate

Optical cover/lens material	Polycarbonate
Fixation material	Aluminum
Mounting device	60 [Spigot for diameter 60 mm]
Optical cover/lens shape	-
Optical cover/lens finish	-
Overall height	990 mm
Overall diameter	560 mm
Effective projected area	0.4396 m ²
Color	Gray
Dimensions (Height x Width x Depth)	990 x NaN x NaN mm (39 x NaN x NaN in)

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level kV

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	2681 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	84 lm/W
Init. Corr. Color Temperature	3000 K
Init. Color Rendering Index	>80
Initial chromaticity	(0.430, 0.300) SDCM <5
Initial input power	25.2 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C


Product Data

Full product code	871829188512200
Order product name	BDS670 GRN30-3S/830 PSR-CLO II MDM 60
EAN/UPC - Product	8718291885122
Order code	88512200
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	910925437984
Net Weight (Piece)	16.610 kg



Metronomis LED Fluid

Dimensional drawing



Metronomis LED BDS650-670

