



Metronomis LED Torch

BDS650 GRN50-3S/830 PSU II MDS C450 60

Metronomis LED, LED GreenLine 5000 lm, Power supply unit (On/Off), Metronomis distribution symmetrical, Spigot for diameter 60 mm

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

Product data

| General Information | | is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components |
|--------------------------|--|---|
| Lamp family code | GRN50 [LED GreenLine 5000 lm] | |
| Light source replaceable | Yes | |
| Number of gear units | 1 unit | |
| Driver included | Yes | |
| Photocell | - | |
| Remarks | *-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there | |
| | | Light source engine type |
| | | LED |
| | | Product family code |
| | | BDS650 [Metronomis LED] |

Metronomis LED Torch

| | |
|---------------------|----------------------------------|
| Lighting Technology | LED |
| Value ladder | Specification |
| Embedded control | - |
| CE mark | Yes |
| Warranty period | 5 years |
| Flammability mark | - |
| ENEC mark | ENEC mark |
| Glow-wire test | Temperature 650 °C, duration 5 s |
| EU RoHS compliant | Yes |

Light Technical

| | |
|------------------------------------|-------------------------------------|
| Standard deviation color matching | 5 |
| Upward light output ratio | 5 |
| Luminous Flux | 4,192 lm |
| Standard tilt angle posttop | - |
| Standard tilt angle side entry | - |
| Correlated Color Temperature (Nom) | 3000 K |
| Luminous Efficacy (rated) (Nom) | 84 lm/W |
| Color rendering index (CRI) | >80 |
| Number of light sources | 1 |
| Light source color | 830 warm white |
| Optical cover type | Polycarbonate bowl/cover |
| Luminaire light beam spread | 17° |
| Optic type outdoor | Metronomis distribution symmetrical |

Operating and Electrical

| | |
|--|---------------------------|
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 to 60 Hz |
| Inrush current | 46 A |
| Inrush time | 0.25 ms |
| Power Consumption | 39.2 W |
| Power Factor (Fraction) | 0.96 |
| Connection | Screw connector |
| Cable | Cable 0.45 m without plug |
| Number of products on MCB of 16 A type B | 11 |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|----------------------------|
| Dimmable | No |
| Driver/power unit/transformer | Power supply unit (On/Off) |
| Constant light output | No |

Mechanical and Housing

| | |
|------------------|----------|
| Housing Material | Aluminum |
|------------------|----------|

| | |
|--------------------------|---------------------------|
| Reflector material | Polycarbonate |
| Optic material | Polycarbonate |
| Optical cover material | Polycarbonate |
| Fixation material | Aluminum |
| Housing Color | Grey |
| Mounting device | Spigot for diameter 60 mm |
| Optical cover shape | - |
| Optical cover finish | - |
| Overall height | 990 mm |
| Overall diameter | 330 mm |
| Effective projected area | 0.274 m² |

Approval and Application

| | |
|--|--|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK10 [20 J vandal-resistant] |
| Surge Protection (Common/Differential) | Philips standard surge protection level |
| Protection class IEC | Safety class II |

Initial Performance (IEC Compliant)

| | |
|---------------------------------------|------------------------|
| Luminous flux tolerance | +/-7% |
| Initial chromaticity | (0.430, 0.300) SDCM <5 |
| Power consumption tolerance | +/-10% |
| Init. Color Rendering Index Tolerance | +/-2 |

Over Time Performance (IEC Compliant)

| | |
|--|------|
| Control gear failure rate at median useful life 100000 h | 10 % |
| Lumen maintenance at median useful life* 100000 h | L80 |

Application Conditions

| | |
|------------------------------------|-------|
| Performance ambient temperature Tq | 25 °C |
|------------------------------------|-------|

Product Data

| | |
|---------------------------------|--|
| Order product name | BDS650 GRN50-3S/830 PSU II MDS C450 60 |
| Full product name | BDS650 GRN50-3S/830 PSU II MDS C450 60 |
| Full product code | 871829188534400 |
| Order code | 88534400 |
| Material Nr. (12NC) | 910925438007 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718291885344 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8718291885344 |

Metronomis LED Torch

Dimensional drawing

