



# Metronomis LED Torch

BDS650 GRN20-3S/740 PSR-CLO II VD C450 6

Metronomis LED, LED GreenLine 2000 lm, Power supply unit regulating with constant light output

Metronomis LED is the first post-top range in the world to offer a palette of environmental lighting effects to give projects a unique contextual or aesthetic touch. An innovative play of reflection, light and shadow creates an environmental pattern on the ground or on the bowl to create additional ambience. Four new iconic designs – with a visual and modular link to Metronomis I – are reduced to the essential elements. During the day, the discreet, transparent design blends into its context, be it contemporary or classical, while its night-time appearance is both functional and decorative. The flexible, modular Metronomis LED comes with a range of columns and a wide variety of optics and effects, enabling architects and lighting designers to create a unified, consistent lighting design that still reflects the differences in urban culture and history.

## Product data

General Information		
Lamp family code	GRN20 [LED GreenLine 2000 lm]	
Light source replaceable	Yes	
Number of gear units	1 unit	
Driver included	Yes	
Photocell	-	
Remarks	* - Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source engine type	LED	
Product family code	BDS650 [Metronomis LED]	
Lighting Technology	LED	
Value ladder	Specification	

# Metronomis LED Torch

Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

## Light Technical

Standard deviation color matching	5
Upward light output ratio	5
Luminous Flux	1,824 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	83 lm/W
Color rendering index (CRI)	>70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	-
Optic type outdoor	-

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	11.856 W
Average CLO power consumption	13.528 W
End CLO power consumption	15.2 W
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	15.2 W
Power Factor (Fraction)	0.94
Connection	Screw connector
Cable	Cable 0.45 m without plug
Number of products on MCB of 16 A type B	20

## Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating with constant light output
Constant light output	Yes

## Mechanical and Housing

Housing Material	Aluminum
------------------	----------

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 mm
Optical cover shape	-
Optical cover finish	-
Overall height	990 mm
Overall diameter	330 mm
Effective projected area	0.274 m²

## Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

## Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

## Product Data

Order product name	BDS650 GRN20-3S/740 PSR-CLO II VD C450 6
Full product name	BDS650 GRN20-3S/740 PSR-CLO II VD C450 6
Full product code	871829188538200
Order code	88538200
Material Nr. (12NC)	910925438011
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291885382
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291885382

## Metronomis LED Torch

### Dimensional drawing

