PHILIPS Lighting



Iridium gen3 LED Mini

BGP381 GRN25/740 I MSO CO GR SP

Iridium gen3 Mini, LED GreenLine 2500 lm, 740 neutral white, Safety class I, Medium wide street optic, Grey, Spigot

Iridium gen3 is the first truly intelligent luminaire designed for seamless connectivity. No hassle in commissioning – just install the luminaire and control it from a distance through CityTouch management software. Remote light management made easy! The new 'plug & play' concept has been designed to ensure safe and easy installation in just three steps: 1. Install the spigot, 2. Plug in the mains, 3. Tilt and close the luminaire. The luminaire's high efficiency at system level ensures significant energy savings compared to existing conventional installations, offering a fast payback. Thanks to its wide choice of lumen packages, optics and color temperatures, Iridium gen3 fits most applications in residential areas. The luminaire's neo-classical design guarantees a consistent look and feel for your surroundings.

Product data

General Information	
Lamp family code	GRN25 [LED GreenLine 2500 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Gear	EB [Electronic]
Driver included	Yes
Photocell	-
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value. * At

	extreme ambient temperatures the luminaire
	might automatically dim down to protect
	components
Light source engine type	LED
Product family code	BGP381 [Iridium gen3 Mini]
Lighting Technology	LED
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s

Iridium gen3 LED Mini

EU RoHS compliant	No
Light Technical	
Upward light output ratio	0
Luminous Flux	2,375 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	148 lm/W
Color rendering index (CRI)	70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	152°
Optic type outdoor	Medium wide street optic

Spigot
Flat
Textured
531 mm
273 mm
156 mm
0.024 m²
156 x 273 x 531 mm
Cover painted

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	4/4 kV
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful	10 %
life 100000 h	
Lumen maintenance at median useful life*	L80
100000 h	

Application Conditions

 Performance ambient temperature Tq
 25 °C

 Maximum dim level
 Not applicable

Prod	luct	Data

Order product name	BGP381 GRN25/740 I MSO CO GR SP
Full product name	BGP381 GRN25/740 I MSO CO GR SP
Full product code	871829190817300
Order code	90817300
Material Nr. (12NC)	910925438266
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291908173
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291908173

Operating and Electric	al
Input Voltage	

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	22 A
Inrush time	0.29 ms
Power Consumption	16 W
Power Factor (Fraction)	0.94
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type	20

-40 to +50 °C

в

Temperature

Housing Color

Ambient temperature range


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum

Grey

Iridium gen3 LED Mini

Dimensional drawing





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 29 - data subject to change