



Selenium LED

BGP340 LED92--3S/740 PSU II DM 48/60

Selenium LED, LED module 9200 lm, Power supply unit (On/Off), Distribution medium, Universal for diameter 48 to 60 mm

Selenium LED is a cost-effective road-lighting luminaire, which delivers over 60% energy saving compared with conventional solutions. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. The LEDGINE technology inside the luminaire ensures an efficient and uniform light distribution, covering the widest possible range of applications. And installation and maintenance could not be simpler: connectors and driver are directly accessible, without the use of tools.

Product data

General Information	
Lamp family code	LED92 [LED module 9200 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Photocell	-
Remarks	*-Per Lighting Europe guidance paper
	"Evaluating performance of LED based
	luminaires - January 2018": statistically there
	is no relevant difference in lumen
	maintenance between B50 and for example
	B10. Therefore, the median useful life (B50)
	value also represents the B10 value.
Light source engine type	LED
Product family code	BGP340 [Selenium LED]
Lighting Technology	LED

Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 960 °C, duration 5 s
EU RoHS compliant	No
Light Technical	
Upward light output ratio	0
Luminous Flux	7,906 lm
Standard tilt angle posttop	O°
Standard tilt angle side entry	O°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	111 lm/W
Color rendering index (CRI)	≥70

Datasheet, 2023, April 30 data subject to change


Selenium LED


Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	160°
Optic type outdoor	Distribution medium
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	150 ms
Power Consumption	71 W
Power Factor (Fraction)	0.95
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type	8
В	
Temperature	
Ambient temperature range	-30 to +45 ℃
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	
Optic material	Glass
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Aluminum and gray
Mounting device	Universal for diameter 48 to 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	750 mm
Overall width	320 mm

Overall height 210 mm Effective projected area 0.07 m² Dimensions (Height x Width x Depth) 210 x 320 x 750 mm Approval and Application Ingress protection code IP66 [Dust penetration-protected, jet-phase in part protection code IK08 [5 J vandal-protected] Surge Protection (Common/Differential) 6/4 kV Protection class IEC Safety class II Initial Performance (IEC Compliant)
Dimensions (Height x Width x Depth) Approval and Application Ingress protection code IP66 [Dust penetration-protected, jet-p Mech. impact protection code IK08 [5 J vandal-protected] Surge Protection (Common/Differential) Frotection class IEC Safety class II Initial Performance (IEC Compliant)
Approval and Application Ingress protection code IP66 [Dust penetration-protected, jet-p Mech. impact protection code IK08 [5 J vandal-protected] Surge Protection (Common/Differential) 6/4 kV Protection class IEC Safety class II Initial Performance (IEC Compliant)
Ingress protection code IP66 [Dust penetration-protected, jet-penetration-protected, jet-penetration-protected] Mech. impact protection code IK08 [5 J vandal-protected] Surge Protection (Common/Differential) 6/4 kV Protection class IEC Safety class II Initial Performance (IEC Compliant)
Ingress protection code IP66 [Dust penetration-protected, jet-penetration-protected, jet-penetration-protected] Mech. impact protection code IK08 [5 J vandal-protected] Surge Protection (Common/Differential) 6/4 kV Protection class IEC Safety class II Initial Performance (IEC Compliant)
Mech. impact protection code IKO8 [5 J vandal-protected] Surge Protection (Common/Differential) 6/4 kV Protection class IEC Safety class II Initial Performance (IEC Compliant)
Surge Protection (Common/Differential) 6/4 kV Protection class IEC Safety class II Initial Performance (IEC Compliant)
Protection class IEC Safety class II Initial Performance (IEC Compliant)
Initial Performance (IEC Compliant)
Luminous flux tolerance +/-7%
Initial chromaticity (0.380, 0.370) SDCM <3
Power consumption tolerance +/-10%
Init. Color Rendering Index Tolerance +/-2
Over Time Performance (IEC Compliant)
Control gear failure rate at median useful 7.5%
life 75000 h
Lumen maintenance at median useful life* L80
75000 h
Application Conditions
Performance ambient temperature Tq 25 °C
Product Data
Product Data Order product name BGP340 LED923S/740 PSU II DM 48/
Order product name BGP340 LED923S/740 PSU II DM 48/
Order product nameBGP340 LED923S/740 PSU II DM 48/Full product nameBGP340 LED923S/740 PSU II DM 48/
Order product name BGP340 LED923S/740 PSU II DM 48/ Full product name BGP340 LED923S/740 PSU II DM 48/ Full product code 871829106350600
Order product name BGP340 LED923S/740 PSU II DM 48/ Full product name BGP340 LED923S/740 PSU II DM 48/ Full product code 871829106350600 Order code 06350600
Order product name BGP340 LED923S/740 PSU II DM 48/ Full product name BGP340 LED923S/740 PSU II DM 48/ Full product code 871829106350600 Order code 06350600 Material Nr. (12NC) 910925438550

8718291063506

Dimensional drawing





EAN/UPC - Case

Selenium LED



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.