



# **Selenium LED**

## BGP340 LED110--3S/740 PSR I DM DDF2 48/6

Selenium LED, LED module 11000 lm, Power supply unit regulating, Distribution medium, DynaDimmer with fixed presets version 2, Universal for diameter 48 to 60 mm

Selenium LED is a cost-effective road-lighting luminaire, which delivers over 60% energy saving compared with conventional solutions. Its simple, rounded form reduces its daytime visual impact, allowing it to integrate into any kind of environment. The LEDGINE technology inside the luminaire ensures an efficient and uniform light distribution, covering the widest possible range of applications. And installation and maintenance could not be simpler: connectors and driver are directly accessible, without the use of tools.

#### **Product data**

| General Information      |   |
|--------------------------|---|
| Lamp family code         | LED110 [LED module 11000 lm]                    |
| Light source replaceable | Yes   |
| Number of gear units     | 1 unit  |
| Driver included          | Yes   |
| Photocell                | -   |
| Remarks                  | *-Per Lighting Europe guidance paper            |
|                          | "Evaluating performance of LED based            |
|                          | luminaires - January 2018": statistically there |
|                          | is no relevant difference in lumen              |
|                          | maintenance between B50 and for example         |
|                          | B10. Therefore, the median useful life (B50)    |
|                          | value also represents the B10 value.            |
| Light source engine type | LED   |
| Product family code      | BGP340 [Selenium LED]                           |

| Lighting Technology                | LED                                     |
|------------------------------------|---|
| Embedded control                   | DynaDimmer with fixed presets version 2 |
| CE mark                            | Yes                                     |
| Warranty period                    | 5 years                                 |
| Flammability mark                  | -                                       |
| ENEC mark                          | ENEC mark                               |
| Glow-wire test                     | Temperature 960 °C, duration 5 s        |
| EU RoHS compliant                  | No                                      |
|                                    |   |
| Light Technical                    |   |
| Upward light output ratio          | 0                                       |
| Luminous Flux                      | 9,381 lm                                |
| Standard tilt angle posttop        | O°                                      |
| Standard tilt angle side entry     | O°                                      |
| Correlated Color Temperature (Nom) | 4000 K                                  |

Datasheet, 2023, April 29 data subject to change


### **Selenium LED**


| Luminous Efficacy (rated) (Nom)         | 110 lm/W   |
|---|--|
| Color rendering index (CRI)             | ≥70  |
| Number of light sources                 | 1  |
| Light source color                      | 740 neutral white                                    |
| Optical cover type                      | Flat glass   |
| Luminaire light beam spread             | 160°   |
| Optic type outdoor                      | Distribution medium                                  |
|   |  |
| Operating and Electrical                |  |
| Input Voltage                           | 220-240 V  |
| Line Frequency                          | 50 to 60 Hz  |
| Inrush current                          | 80 A   |
| Inrush time                             | 150 ms   |
| Power Consumption                       | 85 W   |
| Power Factor (Fraction)                 | 0.95   |
| Connection                              | Screw connection block 3-pole                        |
| Cable                                   | -  |
| Number of products on MCB of 16 A type  | 8  |
| В                                       |  |
|   |  |
| Temperature                             |  |
| Ambient temperature range               | -30 to +45 °C  |
|   |  |
| Controls and Dimming                    |  |
| Dimmable                                | Yes  |
| Driver/power unit/transformer           | Power supply unit regulating                         |
| Control interface                       | Analog   |
| Constant light output                   | No   |
| Mechanical and Housing                  |  |
| Mechanical and Housing Housing Material | Aluminum   |
| Reflector material                      | - Atuminum   |
| Optic material                          | Glass  |
| Optical cover material                  | Glass  |
| Fixation material                       | Stainless steel                                      |
|   |  |
| Housing Color  Mounting dovice          | Aluminum and gray Universal for diameter 48 to 60 mm |
| Mounting device                         | Flat   |
| Optical cover shape                     | Clear  |
| Optical cover finish Overall length     |  |
| Overall length                          | 750 mm   |
| Overall width                           | 320 mm   |

| Effective projected area                     | 210 mm<br>0.07 m <sup>2</sup><br>210 x 320 x 750 mm |
|--|---|
|  |   |
| Dimensions (Height X Width X Depth)          | 210 X 320 X 730 IIIIII                              |
|  |   |
| Approval and Application                     |   |
|  | P66 [Dust penetration-protected, jet-proof]         |
|  | IKO8 [5 J vandal-protected]                         |
|  | 6/4 kV  |
|  | Safety class I                                      |
|  |   |
| Initial Performance (IEC Compliant)          |   |
| Luminous flux tolerance +                    | +/-7%   |
| Initial chromaticity (                       | (0.380, 0.370) SDCM <3                              |
| Power consumption tolerance +                | +/-10%  |
| Init. Color Rendering Index Tolerance        | +/-2  |
|  |   |
| Over Time Performance (IEC Complian          | nt)   |
| Control gear failure rate at median useful 7 | 7.5 %   |
| life 75000 h                                 |   |
| Lumen maintenance at median useful life* L   | L80   |
| 75000 h                                      |   |
|  |   |
| Application Conditions                       |   |
| Performance ambient temperature Tq 2         | 25 °C   |
| Maximum dim level 1                          | 10%   |
|  |   |
| Product Data                                 |   |
| Order product name                           | BGP340 LED1103S/740 PSR I DM DDF2                   |
|  | 48/6  |
| Full product name                            | BGP340 LED1103S/740 PSR I DM DDF2                   |
|  | 48/6  |
| Full product code 8                          | 871829106381000                                     |
| Order code (                                 | 06381000  |
|  | 910925438581  |
| Numerator - Quantity Per Pack                | 1   |
| EAN/UPC - Product/Case                       | 8718291063810                                       |
| Numerator - Packs per outer box 1            | 1   |
| EAN/UPC - Case                               | 8718291063810                                       |

### **Selenium LED**

#### Dimensional drawing









© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.