



CoreLine Trunking

LL121X 7 WH BC

CoreLine Trunking, White

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information	
Angle	-
Accessory color	White
Service tag	Yes
Product family code	LL121X [CoreLine Trunking]
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Connection	Connector with 2 additional wires for light regulation
Temperature	
Ambient temperature range	-20 to +35 °C
Mechanical and Housing	
Housing Color	White

Overall length	1,730 mm
Overall width	81 mm
Overall height	43 mm
Dimensions (Height x Width x Depth)	43 x 81 x 1730 mm
Material	Steel

Approval and Application


Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

Product Data


Order product name	LL121X 7 WH BC
Full product name	LL121X 7 WH BC
Full product code	871829188144500
Order code	88144500
Material Nr. (12NC)	910925682907
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291881445
Numerator - Packs per outer box	1

EAN/UPC - Case	8718291881445
----------------	---------------


Dimensional drawing



Product
LL121X 7 WH BC



Product
LL121X 7 WH BC



Product
LL121X 7 WH BC

CoreLine Trunking

Dimensional drawing

