



# CoreLine Trunking

## LL121X 7 WH BC

### CoreLine Trunking, White


Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

#### Product data

General Information	
Angle	-
Accessory colour	White
Product family code	LL121X [CoreLine Trunking]
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Connection	Connector with 2 additional wires for light regulation
Temperature	
Ambient temperature range	-20 to +35 °C
Mechanical and Housing	
Housing Colour	White
Overall length	1,730 mm


Overall width	81 mm
Overall height	43 mm
Dimensions (height x width x depth)	43 x 81 x 1730 mm
Material	Steel
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Product Data	
Order product name	LL121X 7 WH BC
Full product name	LL121X 7 WH BC
Full EOC	871829188144500
Order code	88144500
Material no. (12 NC)	910925682907
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291881445
Numerator – packs per outer box	1
EAN/UPC – Case	8718291881445

Dimensional drawing




Product

LL121X 7 WH BC



Product

LL121X 7 WH BC



Product

LL121X 7 WH BC

## CoreLine Trunking

### Dimensional drawing

