



# CoreLine Trunking

## LL121X LED45S/840 1x PSU MB 5 WH

CoreLine Trunking, LED Module, system flux 4500 lm, Power supply unit (On/Off), Medium beam

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information		Flammability mark	
Lamp family code	LED45S [LED Module, system flux 4500 lm]	For mounting on normally flammable surfaces	
Light source replaceable	No	ENEC mark	
Number of gear units	1 unit	Glow-wire test	
Driver included	Yes	Temperature 650 °C, duration 5 s	
Feed-through wiring	Feed-through wiring 5-phase	EU RoHS compliant	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Light Technical	
Service tag	Yes	Luminous Flux	
Product family code	LL121X [CoreLine Trunking]	4,500 lm	
Lighting Technology	LED	Correlated Color Temperature (Nom)	
CE mark	Yes	4000 K	
Warranty period	3 years	Luminous Efficacy (rated) (Nom)	
		141 lm/W	
		Color rendering index (CRI)	
		≥80	
		Number of light sources	
		3	
		Beam angle of light source	
		120 degree(s)	
		Light source color	
		840 neutral white	
		Optic type	
		Medium beam	
		Optical cover type	
		-	
		Luminaire light beam spread	
		76° x 74°	

## CoreLine Trunking

Unified glare rating CEN	Not applicable
--------------------------	----------------

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	32 W
Power Factor (Fraction)	0.95
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24

### Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover material	Acrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,730 mm
Overall width	95 mm
Overall height	52 mm
Dimensions (Height x Width x Depth)	52 x 95 x 1730 mm

### Approval and Application

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80


### Application Conditions

Performance ambient temperature Tq	25 °C
Suitable for random switching	No

### Product Data

Order product name	LL121X LED45S/840 1x PSU MB 5 WH
Full product name	LL121X LED45S/840 1x PSU MB 5 WH
Full product code	871829188171100
Order code	88171100
Material Nr. (12NC)	910925682914
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291881711
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291881711

## Dimensional drawing



### Dimensional drawing

#### Product

LL121X LED45S/840 1x PSU MB 5 WH

