



CoreLine Trunking

LL121X LED45S/840 1x PSU WB 5 WH

CoreLine Trunking, LED Module, system flux 4500 lm, Power supply unit (On/Off), Wide beam

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data


General Information			
Lamp family code	LED45S [LED Module, system flux 4500 lm]	Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No	ENEC mark	ENEC mark
Number of gear units	1 unit	Glow-wire test	Temperature 650 °C, duration 5 s
Driver included	Yes	EU RoHS compliant	Yes
Feed-through wiring	Feed-through wiring 5-phase	Light Technical	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	Luminous Flux	4,500 lm
Service tag	Yes	Correlated Color Temperature (Nom)	4000 K
Product family code	LL121X [CoreLine Trunking]	Luminous Efficacy (rated) (Nom)	141 lm/W
Lighting Technology	LED	Color rendering index (CRI)	≥80
CE mark	Yes	Number of light sources	3
Warranty period	3 years	Beam angle of light source	120 degree(s)
		Light source color	840 neutral white
		Optic type	Wide beam
		Optical cover type	-
		Luminaire light beam spread	88° x 94°

CoreLine Trunking

Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	19 A
Inrush time	0.28 ms
Power Consumption	32 W
Power Factor (Fraction)	0.95
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	-20 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No
Mechanical and Housing	
Housing Material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover material	Acrylate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear
Overall length	1,730 mm
Overall width	95 mm
Overall height	52 mm
Dimensions (Height x Width x Depth)	52 x 95 x 1730 mm

Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%
Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	No
Product Data	
Order product name	LL121X LED45S/840 1x PSU WB 5 WH
Full product name	LL121X LED45S/840 1x PSU WB 5 WH
Full product code	871829188177300
Order code	88177300
Material Nr. (12NC)	910925682920
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291881773
Numerator - Packs per outer box	1
EAN/UPC - Case	8718291881773

Dimensional drawing



Dimensional drawing

Product

LL121X LED45S/840 1x PSU WB 5 WH

