



CoreLine Trunking

LL121X LED45S/840 1x PSU NB 5 WH

CoreLine Trunking - LED Module, system flux 4500 lm - Power supply unit - Narrow beam

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information		Mounting	
Number of light sources	3 [3 pcs]	Ready-to-install	-
Lamp family code	LED45S [LED Module, system flux 4500 lm]	Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Beam angle of light source	120 °	Flammability mark	F [For mounting on normally flammable surfaces]
Light source colour	840 neutral white	Accessories included	MB-SW [Mounting bracket for suspension wire]
Light source replaceable	No	CE mark	CE mark
Number of gear units	1 unit	ENEC mark	ENEC mark
Driver/power unit/transformer	PSU [Power supply unit]	Warranty period	3 years
Driver included	Yes	Mechanical accessories	No [-]
Optic type	NB [Narrow beam]	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Optical cover/lens type	No [-]		
Luminaire light beam spread	20° x 68°		
Emergency lighting	No [-]		
Internal wiring	Standard		
Feed-through wiring	Feed-through wiring 5-phase		
Connection	CU5 [Connection unit 5-pole]		
Cable	-		
Protection class IEC	Safety class I (I)		

CoreLine Trunking

Constant light output	No
Number of products on MCB	24
Product Family Code	LL121X [CoreLine Trunking]
Unified glare rating CEN	Not applicable

Light Technical

Light distribution	DIR [Direct lighting]
--------------------	------------------------

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Circuit	No [-]
Circuit option	5 [5 conductors]
Inrush current	19 A
Inrush time	0.28 ms
Power factor (min.)	0.95

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	1730 mm
Overall width	95 mm
Overall height	52 mm
Height	52 mm
Diameter	-
Colour	White
Dimensions (height x width x depth)	52 x 95 x 1730 mm (2 x 3.7 x 68.1 in)

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	--------------------------

Mech. impact protection code	IK02 [0.2 J standard]
------------------------------	------------------------

Initial Performance (IEC Compliant)

Initial luminous flux	4500 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	141 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	32 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

Application Conditions

Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Suitable for random switching	No

Product Data

Full product code	871829188435400
Order product name	LL121X LED45S/840 1x PSU NB 5 WH
EAN/UPC – product	8718291884354
Order code	88435400
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925682955
Net weight (piece)	3.650 kg



