



CoreLine Trunking

LL123X 5C6 7

CoreLine Trunking

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information	
Protection class IEC	Safety class I (I)
CE mark	CE mark
ENEC mark	ENEC mark
Material	Steel
Angle	-
Accessory colour	White
Product Family Code	LL123X [CoreLine Trunking]

Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz

Mechanical and Housing	
Overall length	1730 mm
Overall width	81 mm
Overall height	43 mm
Dimensions (height x width x depth)	43 x 81 x 1730 mm (1.7 x 3.2 x 68.1 in)


Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]

Product Data	
Full product code	871829190798500
Order product name	LL123X 5C6 7
EAN/UPC – product	8718291907985
Order code	90798500
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925683073
Net weight (piece)	2.700 kg



CoreLine Trunking

Dimensional drawing



LL123X Light-line units

