



TownGuide Performer

BDP103 LED70/740 DS PCC GR D9 62P

TOWNGUIDE PERF CLASSIC T, LED module 7000 lm, Distribution symmetrical, Polycarbonate bowl/cover clear, Post-top for diameter 62 mm

The TownGuide Performer family consists of six recognizable, yet modern shapes: Flat Cone, Bowl, Classic Cone, Classic T, T and Tzero. Each luminaire has the option of a clear (PCC), translucent (PCTR) or frosted (PCF) bowl (except Tzero, which is only available with a clear bowl). With an extensive range of lumen packages, neutral white or warm white LED lights sources, and a range of dedicated optics for lower mounting heights, it's easy to select the version that best suits the specific requirements of your project. All this combined with a long life expectancy of 100,000 operating hours. In addition, TownGuide Performer has a variety of control system options that can make this luminaire an integral part of smart energy-reduction programs. This includes LumiStep, DynaDimmer, and LineSwitch stand-alone dim control, and Coded Mains group control, right up to seamless remote connectivity with Interact lighting management software. Installation is easy. Thanks to the bayonet whistle connector with integrated gland located in the spigot, there's no need to open the luminaire for installation. The Signify Service tag app offers direct access to all relevant data, ensuring maintenance is easy too. Philips has made every effort to make the Total Cost of Ownership (TCO) of the luminaire as attractive as possible. And as TownGuide Performer is a dedicated LED luminaire, compatible with a variety of control systems, there are significant energy and maintenance cost savings compared with conventional lighting.

Product data

General Information		Number of gear units	
Lamp family code	LED70 [LED module 7000 lm]	Driver included	Yes
Light source replaceable	Yes	Photocell	-

TownGuide Performer

Light source engine type	LED
Service tag	Yes
Product family code	BDP103 [TOWNGUIDE PERF CLASSIC T]
Lighting Technology	LED
Value ladder	Performance
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes
Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection device, optics, front cover and mechanical parts

Light Technical

Upward light output ratio	3
Luminous Flux	5,320 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	117 lm/W
Color rendering index (CRI)	70
Number of light sources	8
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	75°
Optic type outdoor	Distribution symmetrical

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	45 A
Inrush time	0.285 ms
Power Consumption	45.5 W
Power Factor (Fraction)	0.96
Connection	Screw connection block 5-pole
Cable	-
Number of products on MCB of 16 A type B	10

Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI

Constant light output	No
-----------------------	----

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	Gray
Mounting device	Post-top for diameter 62 mm
Optical cover shape	Wide
Optical cover finish	Clear
Overall length	570 mm
Overall width	570 mm
Overall height	458 mm
Overall diameter	570 mm
Effective projected area	0.093 m ²
Dimensions (Height x Width x Depth)	458 x 570 x 570 mm
Parts color	All parts colored

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	93

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

Product Data

Order product name	BDP103 LED70/740 DS PCC GR D9 62P
Full product name	BDP103 LED70/740 DS PCC GR D9 62P
Full product code	871869634712600
Order code	910925863301
Material Nr. (12NC)	910925863301
Numerator - Quantity Per Pack	1

TownGuide Performer

EAN/UPC - Product/Case	8718696347126
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696347126

Dimensional drawing

