



Iridium gen3 LED Mini

BGP381 GRN17/740 II WSO CO GR MSP CLO-DD

Iridium gen3 Mini, LED GreenLine 1700 lm, 740 neutral white, Safety class II, Wide street optic, Grey, Constant light output and DynaDimmer fixed presets version 6, Luminaire surge protection level until 10 kV differential mode and 10 kV common mode

Iridium gen3 is the first truly intelligent luminaire designed for seamless connectivity. No hassle in commissioning – just install the luminaire and control it from a distance through CityTouch management software. Remote light management made easy! The new ‘plug & play’ concept has been designed to ensure safe and easy installation in just three steps: 1. Install the spigot, 2. Plug in the mains, 3. Tilt and close the luminaire. The luminaire’s high efficiency at system level ensures significant energy savings compared to existing conventional installations, offering a fast payback. Thanks to its wide choice of lumen packages, optics and color temperatures, Iridium gen3 fits most applications in residential areas. The luminaire’s neo-classical design guarantees a consistent look and feel for your surroundings.

Product data

General Information		B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Lamp family code	GRN17 [LED GreenLine 1700 lm]		
Light source replaceable	Yes		
Number of gear units	1 unit		
Gear	EB [Electronic]		
Driver included	Yes		
Remarks	*-Per Lighting Europe guidance paper “Evaluating performance of LED based luminaires – January 2018”: statistically there is no relevant difference in lumen maintenance between B50 and for example		
		Light source engine type	LED
		Product family code	BGP381 [Iridium gen3 Mini]
		Lighting Technology	LED
		Embedded control	Constant light output and DynaDimmer fixed presets version 6
		CE mark	Yes

Iridium gen3 LED Mini

Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	No

Light Technical

Upward light output ratio	0
Luminous Flux	1,520 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	136 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	152°
Optic type outdoor	Wide street optic

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	11.2 W
Average CLO power consumption	11.4 W
End CLO power consumption	11.6 W
Inrush current	15 A
Inrush time	0.36 ms
Power Consumption	11.6 W
Power Factor (Fraction)	0.96
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	23

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DynaDimmer and constant light output (integrated)
Control interface	-
Constant light output	Yes

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum

Housing Color	Grey
Mounting device	Spigot
Optical cover shape	Flat
Optical cover finish	Textured
Overall length	531 mm
Overall width	273 mm
Overall height	156 mm
Effective projected area	0.024 m²
Dimensions (Height x Width x Depth)	156 x 273 x 531 mm
Parts color	Cover painted

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L100

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	50%

Product Data

Order product name	BGP381 GRN17/740 II WSO CO GR MSP CLO-DD
Full product name	BGP381 GRN17/740 II WSO CO GR MSP CLO-DD
Full product code	871869637708600
Order code	910925863583
Material Nr. (12NC)	910925863583
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696377086
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696377086

Iridium gen3 LED Mini

Dimensional drawing

