



DigiStreet

BGP763 LED340-/740 II DW10 DGR SRG10 62

DigiStreet Large, LED module 34000 lm, 740 neutral white, Safety class II, Distribution wide 12, Dark gray, Luminaire surge protection level until 10 kV differential mode and 10 kV common mode, Spigot for diameter 60 mm

Developed with the aim to become your long term partner, the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the Philips CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		
Lamp family code	LED340 [LED module 34000 lm]	
Light source replaceable	No	
Number of gear units	2 units	
Gear	EB [Electronic]	
Driver included	Yes	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen	maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.
		Light source engine type
		LED
		Product family code
		BGP763 [DigiStreet Large]
		Lighting Technology
		LED
		Value ladder
		Specification
		CE mark
		Yes
		Warranty period
		5 years
		Flammability mark
		-

ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 5 s
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	29,580 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	144 lm/W
Color rendering index (CRI)	70
Number of light sources	1
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	-
Optic type outdoor	Distribution wide 12

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	205 W
Power Factor (Fraction)	0.99
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B 4	

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Dark gray

Mounting device	Spigot for diameter 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	1,011 mm
Overall width	361 mm
Overall height	121 mm
Effective projected area	0.08 m²
Dimensions (Height x Width x Depth)	121 x 361 x 1011 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L84

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP763 LED340-/740 II DW10 DGR SRG10 62
Full product name	BGP763 LED340-/740 II DW10 DGR SRG10 62
Full product code	871869637844100
Order code	910925863721
Material Nr. (12NC)	910925863721
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696378441
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696378441

Dimensional drawing

