



Pacific LED gen4

WT470C LED23S/840 PSU VWB L1300

PACIFIC LED WATERPROOF, 840 neutral white, Power supply unit (On/Off), Very wide beam, Screw connection with pug and socket

PacificLED gen4 is a highly efficient and reliable LED waterproof luminaire that offers an excellent quality of light, with a uniform light distribution without visible striping or color artefacts. The range offers modular construction to enable ease of upgrade and maintenance. The new optical system provides distortion-free lighting with improved visual guidance, which makes it ideally suited to general industry, warehouses and parking areas. The range also offers the option of multiple optics to ensure an optimized lighting scheme for a wide range of applications. For industrial applications, PacificLED gen4 offers an open product architecture with toolless access to the gear tray and an innovative end-cap design with built-in connector for fast and easy installation. The single-piece mounting clamp ensures no small, loose components which could affect the primary production process.

Product data

General Information		Product family code	WT470C [PACIFIC LED WATERPROOF]
Light source replaceable	Yes	Lighting Technology	LED
Number of gear units	1 unit	Value ladder	Specification
Driver included	Yes	CE mark	Yes
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.		
		Warranty period	5 years
		Flammability mark	For mounting on easily flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 850 °C, duration 5 s
		EU RoHS compliant	Yes

Pacific LED gen4

Light Technical	
Luminous Flux	2,300 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	>80
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Very wide beam
Luminaire light beam spread	120° x 120°
Unified glare rating CEN	22

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	15.1 A
Inrush time	0.23 ms
Power Consumption	16.4 W
Power Factor (Fraction)	0.96
Connection	Screw connection with pug and socket
Cable	-
Number of products on MCB of 16 A type B	32

Temperature	
Ambient temperature range	-25 to +45 °C

Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing	
Housing Material	Polycarbonate
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Clear

Overall length	1,321 mm
Overall width	96 mm
Overall height	108 mm
Dimensions (Height x Width x Depth)	108 x 96 x 1321 mm

Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life 50000 h	5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 50000 h	L90

Application Conditions	
Performance ambient temperature Tq	25 °C
Suitable for random switching	Not applicable

Product Data	
Order product name	WT470C LED23S/840 PSU VWB L1300
Full product name	WT470C LED23S/840 PSU VWB L1300
Full product code	871869637919600
Order code	910925863796
Material Nr. (12NC)	910925863796
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696379196
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696379196

Pacific LED gen4

Dimensional drawing

