



LumiStreet

BGS212 ECO41/740 II 48/60A

LumiStreet Mini, LED EconomyLine 4100 lm, 740 neutral white, Safety class II, Distribution medium, Universal for diameter 48 to 60 mm adjustable

Many local authorities today have an outdated public lighting installation that urgently needs to be replaced, yet have only a limited budget available. We have the answer to their needs. With its compact design and modern LED architecture, LumiStreet is a versatile, cost-effective luminaire that fulfils basic functional road lighting requirements. It is made of high-quality components that ensure long lifetime and low maintenance cost. The result? A road lighting luminaire that provides effective illumination while at the same time cutting energy and maintenance bills. Core version design for high-volume projects at relatively low initial budget. Offer limited range of optics. Performer version design for customer who are preparing big renovation projects, TCO oriented.

Warnings and Safety

- PLEASE NOTE LUMISTREET SMALL IS NOT AVAILABLE FOR SALE IN UK & IRELAND; SAME HAS BEEN REPLACED BY LUMISTREET MINI

Product data

General Information		
Lamp family code	ECO41 [LED EconomyLine 4100 lm]	
Light source replaceable	Yes	
Number of gear units	Unit	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there	is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components

Light source engine type	LED
Product family code	BGS212 [LumiStreet Mini]
Lighting Technology	LED
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upwards light output ratio	0
Luminous Flux	4,100 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	128 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	154°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	27 A
Inrush time	29 ms
Power Consumption	31.6 W
Power Factor (Fraction)	0.98
Connection	Screw connection block 3-pole
Cable	-
Number of products on MCB of 16 A type B	18

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium die cast
------------------	--------------------

Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Tempered glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Universal for diameter 48 to 60 mm adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	505 mm
Overall width	270 mm
Overall height	98 mm
Effective projected area	0.0356 m²
Dimensions (height x width x depth)	98 x 270 x 505 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge-protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BGS212 ECO41/740 II 48/60A
Full product name	BGS212 ECO41/740 II 48/60A
Full EOC	871869638196000
Order code	38196000
Material no. (12 NC)	910925864076
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696381960
Numerator – packs per outer box	1
EAN/UPC - Case	8718696381960

Dimensional drawing

