



ClearWay gen2

BGP307 LED35/740 II DM 48/60S

ClearWay gen2, LED module 3500 lm, 740 neutral white, Safety class II, Distribution medium, Universal for diameter 48 to 60 mm adjustable

The ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimise your Total Cost of Ownership. The ClearWay Gen2 significantly improves the most important aspects of the street-lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good-quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design which makes it easier to install.

Product data

General Information	
Lamp family code	LED35 [LED module 3500 lm]
Light source replaceable	Yes
Number of gear units	Unit
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance
	paper 'Evaluating performance of LED based
	luminaires – January 2018': statistically there
	is no relevant difference in lumen
	maintenance between the B50 and, for
	example, the B10. Therefore, the median
	useful life (B50) value also represents the B10

	value. * At extreme ambient temperatures the
	luminaire might automatically dim down to
	protect components
Light source engine type	LED
Product family code	BGP307 [ClearWay gen2]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark

Datasheet, 2023, December 5 data subject to change

ClearWay gen2

EU RoHS compliant Light Technical Upwards light output ratio	Yes
	0
Luminous Flux	3.115 lm
	0°
Standard tilt angle post-top	0°
Standard tilt angle side entry	·
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	127 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optic type	-
Optical cover type	Flat glass
Luminaire light beam spread	42° x 44°
Optic type outdoor	Distribution medium
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	24.5 W
Power Factor (Fraction)	0.91
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type	11
В	
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium die cast
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Tempered glass
Fixation material	Aluminium
	Aluminium Grey
Fixation material	

Overall length 48 Overall width 32 Overall height 150 Effective projected area 0.1	ear 80 mm 15 mm 0 mm
Overall length 48 Overall width 32 Overall height 150 Effective projected area 0.1 Dimensions (height x width x depth) 150	30 mm 15 mm 0 mm
Overall width 32 Overall height 150 Effective projected area 0.1 Dimensions (height x width x depth) 150	5 mm 0 mm
Overall height 156 Effective projected area 0.1 Dimensions (height x width x depth) 156	0 mm
Effective projected area 0.1 Dimensions (height x width x depth) 150	
Dimensions (height x width x depth) 150	1151 m²
Approval and Application	0 x 325 x 480 mm
Approval and Application	
Approvat and Application	
Ingress protection code IP6	66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	09 [10 J]
Surge Protection (Common/Differential) Lu	ıminaire surge protection level up to 6 kV
dif	fferential mode and 8 kV common mode
Sustainability rating -	
Protection class IEC Sa	afety class II
Photobiological risk Ph	notobiological risk group 1 @ 200mm to
EN	N62471
Photobiological risk specification 3.1	l m
Initial Performance (IEC Compliant)	
Luminous flux tolerance +/-	-7%
Initial chromaticity (0.	.38, 0.38) SDCM <5
	-10%
Init. Color Rendering Index Tolerance +/-	
,	
Over Time Performance (IEC Compliant	t)
	5 %
Control gear failure rate at median useful 10	
life 100,000 h	
Lumen maintenance at median useful L9	77
life* 100,000 h	•
Application Conditions	
	5°C
<u>.</u>	ot applicable
Triaximam dim tevet	эт аррисавте
Product Data	
	GP307 LED35/740 II DM 48/60S
	GP307 LED35/740 II DM 48/60S
	7869698786500
	0035864574
	0925864574
SAP numerator – quantity per pack 1	MOCO COOTOCE
· · · · · · · · · · · · · · · · · · ·	⁷ 18696987865
Numerator – packs per outer box 1	
EAN/UPC - Case 87	¹ 18696987865

ClearWay gen2

Dimensional drawing





