



ClearWay gen2

BGP307 LED99-4S/740 I DM50 48/60S

ClearWay gen2, LED module 9900 lm, 740 neutral white, Safety class I, Distribution medium 50, Universal for diameter 48 to 60 mm adjustable

The ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimise your Total Cost of Ownership. The ClearWay Gen2 significantly improves the most important aspects of the street-lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good-quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design which makes it easier to install.

Product data

General Information			
Lamp family code	LED99 [LED module 9900 lm]	value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Light source replaceable	Yes		
Number of gear units	Unit		
Driver included	Yes	Light source engine type	LED
Remarks	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10	Product family code	BGP307 [ClearWay gen2]
		Lighting Technology	LED
		Value ladder	Performance
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark

ClearWay gen2

EU RoHS compliant	No
-------------------	----

Light Technical

Upwards light output ratio	0
Luminous Flux	8,600 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	146 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optic type	-
Optical cover type	Flat glass
Luminaire light beam spread	154° - 31° x 54°
Optic type outdoor	Distribution medium 50

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	47 A
Inrush time	0.25 ms
Power Consumption	59 W
Power Factor (Fraction)	0.99
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	10

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover/lens material	Tempered glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Universal for diameter 48 to 60 mm adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear

Overall length	482 mm
Overall width	330 mm
Overall height	93 mm
Effective projected area	0.1151 m²
Dimensions (height x width x depth)	93 x 330 x 482 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @ 200mm to EN62471
Photobiological risk specification	3.1 m

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.5 %
Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L96

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP307 LED99-4S/740 I DM50 48/60S
Full product name	BGP307 LED99-4S/740 I DM50 48/60S
Full EOC	871869698804600
Order code	98804600
Material no. (12 NC)	910925864592
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696988046
Numerator – packs per outer box	1
EAN/UPC – Case	8718696988046

ClearWay gen2

Dimensional drawing

