



CoreLine Recessed

RC134B LED37S/840 PSU W60L60 NOC

Coreline Recessed - 840 neutral white - Power supply unit

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Recessed range of LED products can be used to replace functional luminaires in general lighting applications. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

General Information	
Light source colour	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	WB [Wide beam]
Luminaire light beam spread	93°
Control interface	-
Connection	PIP [Push-in connector and pull relief]
Cable	-
Protection class IEC	Safety class I (I)
Glow-wire test	850/30 [Temperature 850 °C, duration 30 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Remarks	*-Per Lighting Europe guidance paper *Evaluating performance of LED based

Constant light output	No	luminaires - January 2018*: statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore the median useful life (B50) value also represents the B10 value.
Number of products on MCB	24	
Product Family Code	RC134B [Coreline Recessed]	
Unified glare rating CEN	22	
Operating and Electrical		
Input voltage	220 to 240 V	
Input frequency	50 to 60 Hz	
Inrush current	8 A	
Inrush time	0.06 ms	
Power factor (min.)	0.9	
Controls and Dimming		
Dimmable	No	

CoreLine Recessed

Mechanical and Housing

Housing material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Textured
Overall length	597 mm
Overall width	597 mm
Overall height	41 mm
Colour	White
Dimensions (height x width x depth)	41 x 597 x 597 mm (1.6 x 23.5 x 23.5 in)

Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK02 [0.2 J standard]

Initial Performance (IEC Compliant)

Initial luminous flux	3700 lm
Luminous flux tolerance	+/-8%
Initial LED luminaire efficacy	109 lm/W
Init. Corr. colour temperature	4000 K
Init. colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	34 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L75

Application Conditions


Ambient temperature range	+10 to +40 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable
Suitable for random switching	Yes

Product Data

Full product code	871869934817500
Order product name	RC134B LED375/840 PSU W60L60 NOC
EAN/UPC – product	8718699348175
Order code	34817500
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	910925864775
Net weight (piece)	3.200 kg



Dimensional drawing



CoreLine Recessed RC134B/RC135B

CoreLine Recessed

