PHILIPS Lighting



ClearWay

BGP303 LED25-4S/740 PSU I DM11 C450CE 42

ClearWay, LED Module 2500 lm, 740 neutral white, Power supply unit (On/Off), Safety class I, Distribution medium 11, Philips standard surge protection level, Cable 0.45 m with connector 3-pole, Universal for diameter 42 to 60 mm

LED technology represents a breakthrough in lighting in many different respects. The light quality provided by LEDs, for example, has made our roads safer, while the tremendous efficacy of LEDs is helping cities reduce their energy bills. At Philips, we believe we can make even more roads safer, and help more municipalities achieve their goal of reducing energy consumption. That's why we have developed ClearWay – a LED road luminaire that is affordable yet does not compromise on light quality and energy efficiency.

Product data

General Information	
Lamp family code	LED25 [LED Module 2500 lm]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Product family code	BGP303 [ClearWay]
Lighting Technology	LED
Flammability mark	For mounting on normally flammable
	surfaces
CE mark	Yes
ENEC mark	ENEC mark
Warranty period	5 years

EU RoHS compliant	No
Light Technical	
Upward light output ratio	0
Luminous Flux	2,225 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	132 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	150° x 62°

ClearWay

Optic type outdoor	Distribution medium 11
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
End CLO power consumption	- W
Inrush current	27 A
Inrush time	0.265 ms
Power Consumption	16.9 W
Power Factor (Fraction)	0.94
Connection	Screw connection block 5-pole
Cable	Cable 0.45 m with connector 3-pole
Number of products on MCB of 16 A ty	pe B 18

Overall height	97 mm
Effective projected area	0.029 m²
Dimensions (Height x Width x Depth)	97 x 330 x 481 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compli	ant)
Driver failure rate at 5000 h	0.5 %
Driver failure rate at 5000 h Application Conditions	0.5 %
	0.5 % Not applicable
Application Conditions	
Application Conditions Maximum dim level	Not applicable
Application Conditions Maximum dim level Product Data	
Application Conditions Maximum dim level Product Data	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450Cl 42
Application Conditions Maximum dim level Product Data Order product name	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C
Application Conditions Maximum dim level Product Data Order product name	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C 42 BGP303 LED25-4S/740 PSU I DM11 C450C
Application Conditions Maximum dim level Product Data Order product name Full product name	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C 42 BGP303 LED25-4S/740 PSU I DM11 C450C 42
Application Conditions Maximum dim level Product Data Order product name Full product name Full product code	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C 42 BGP303 LED25-4S/740 PSU I DM11 C450C 42 871869934904200
Application Conditions Maximum dim level Product Data Order product name Full product name Full product code Order code	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C 42 BGP303 LED25-4S/740 PSU I DM11 C450C 42 871869934904200 910925864863
Application Conditions Maximum dim level Product Data Order product name Full product name Full product code Order code Material Nr. (12NC)	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C 42 BGP303 LED25-4S/740 PSU I DM11 C450C 42 871869934904200 910925864863 910925864863
Application Conditions Maximum dim level Product Data Order product name Full product name Full product code Order code Material Nr. (12NC) Numerator - Quantity Per Pack	Not applicable BGP303 LED25-4S/740 PSU I DM11 C450C 42 BGP303 LED25-4S/740 PSU I DM11 C450C 42 871869934904200 910925864863 910925864863 1

Temperature

Ambient temperature range

Controls and Dimming

•	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

-30 to +35 °C

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Tempered glass
Fixation material	Steel
Housing Color	Grey
Mounting device	Universal for diameter 42 to 60 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	481 mm
Overall width	330 mm

Dimensional drawing



ClearWay



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, September 4 - data subject to change