



ClearWay gen2

BGP307 LED99-4S/740 II DM11 CLO-DDF2 D18

ClearWay gen2, LED module 9900 lm, 740 neutral white, Safety class II, Distribution medium 11, Universal for diameter 48 to 60 mm adjustable

The ClearWay Gen2 enables you to enjoy the benefits of LED technology for urban lighting right from the start. This new second generation of the luminaire builds on the strengths of its predecessor and is designed to further minimise your Total Cost of Ownership. The ClearWay Gen2 significantly improves the most important aspects of the street-lighting experience compared to conventional urban lighting. Ideal for new streets and for renovating existing installations, this affordable range of urban ClearWay lighting solutions combines clean design, high-quality light with significant energy and maintenance savings. In short, ClearWay Gen2 means good-quality light with all the added benefits of LED – energy savings and long lifetime. Offering more benefits, yet packaged in a thinner and lighter design which makes it easier to install.

Product data

General Information		
Lamp family code	LED99 [LED module 9900 lm]	
Light source replaceable	Yes	
Number of gear units	Unit	
Driver included	Yes	
Remarks	*- According to the Lighting Europe guidance	
	paper 'Evaluating performance of LED based	
	luminaires – January 2018': statistically there	
	is no relevant difference in lumen	
	maintenance between the B50 and, for	
	example, the B10. Therefore, the median	
	useful life (B50) value also represents the B10	

	value. * At extreme ambient temperatures the
	luminaire might automatically dim down to
	protect components
Light source engine type	LED
Product family code	BGP307 [ClearWay gen2]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark

Datasheet, 2023, December 5 data subject to change

ClearWay gen2

256 lm 2000 K 7 lm/W 0 10 neutral white	Optical cover/lens finish Overall length Overall width Overall height Effective projected area Dimensions (height x width x depth) Approval and Application Ingress protection code Mech. impact protection code	Clear 482 mm 330 mm 93 mm 0.1151 m² 93 x 330 x 482 mm IP66 [Dust penetration-protected, jet-proof]
000 K 7 lm/W	Overall width Overall height Effective projected area Dimensions (height x width x depth) Approval and Application Ingress protection code	330 mm 93 mm 0.1151 m ² 93 x 330 x 482 mm
000 K 7 lm/W	Overall height Effective projected area Dimensions (height x width x depth) Approval and Application Ingress protection code	93 mm 0.1151 m² 93 x 330 x 482 mm
000 K 7 lm/W	Effective projected area Dimensions (height x width x depth) Approval and Application Ingress protection code	0.1151 m ² 93 x 330 x 482 mm
000 K 7 lm/W	Dimensions (height x width x depth) Approval and Application Ingress protection code	93 x 330 x 482 mm
000 K 7 lm/W	Approval and Application Ingress protection code	
000 K 7 lm/W	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
7 lm/W	Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
)		IP66 [Dust penetration-protected, jet-proof]
	Mech. impact protection code	
10 neutral white		IK09 [10 J]
	Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV
		differential mode and 8 kV common mode
at glass	Sustainability rating	Lighting for circularity
0° - 42° x 54°	Protection class IEC	Safety class II
stribution medium 11	Photobiological risk	Photobiological risk group 1 @ 200mm to
		EN62471
	Photobiological risk specification	3.1 m
20 to 240 V		
) to 60 Hz	Initial Performance (IEC Compliant)	
5 W	Luminous flux tolerance	+/-7%
7 W	Initial chromaticity	(0.38, 0.38) SDCM <5
3 W	Power consumption tolerance	+/-10%
7 A	Init. Color Rendering Index Tolerance	+/-2
25 ms		
5 W	Over Time Performance (IEC Compl	iant)
99	Control gear failure rate at median useful	5 %
ush-in connector 5-pole	life 50,000 h	
	Control gear failure rate at median useful	. 10 %
	life 100,000 h	
	Lumen maintenance at median useful	L100
	life* 100,000 h	
10 to +50 °C	Application Conditions	
	Performance ambient temperature Tq	25 ℃
	Maximum dim level	0% (digital)
es		
ower supply unit with DynaDimmer	Product Data	
	Order product name	BGP307 LED99-4S/740 II DM11 CLO-DDF2
es		D18
	Full product name	BGP307 LED99-4S/740 II DM11 CLO-DDF2
		D18
uminium die cast	Full EOC	871869699730700
	Order code	99730700
olymethyl methacrylate	Material no. (12 NC)	910925865252
empered glass	SAP numerator – quantity per pack	1
uminium	EAN/UPC — Product/Case	8718696997307
rey	Numerator – packs per outer box	1
niversal for diameter 48 to 60 mm	EAN/UPC - Case	8718696997307
djustable		
at		
100 100	or - 42° x 54° stribution medium 11 or to 240 V to 60 Hz W W W A 25 ms W 99 sh-in connector 5-pole or to +50 °C s wer supply unit with DynaDimmer s uminium die cast lymethyl methacrylate mpered glass uminium ey iversal for diameter 48 to 60 mm justable	Protection class IEC Photobiological risk Photobiological risk Photobiological risk specification O to 240 V to 60 Hz Uninious flux tolerance Initial Performance (IEC Compliant) W Initial Performance (IEC Compliant) W Power consumption tolerance Init. Color Rendering Index Tolerance Init. Color Rendering Index Tolerance Init. Other Rendering Index Tolerance Over Time Performance (IEC Compliant) Control gear failure rate at median useful life 50,000 h Control gear failure rate at median useful life 100,000 h Lumen maintenance at median useful life* 100,000 h Application Conditions Performance ambient temperature Tq Maximum dim level S Product Data Order product name Full EOC Order code Ilymethyl methacrylate Impered glass Iminium Eay Inversal for diameter 48 to 60 mm Initial Performance (IEC Compliant) Initial Performance (IEC

ClearWay gen2

Dimensional drawing





