



Mini 300 LED gen3

BBP333 LED81/740 I PRM

Mini 300 LED gen3, LED module 8100 lm, 740 neutral white, Power supply unit (On/Off), Safety class I, Petrol rotational symmetric medium, White

Philips Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on demand intelligent motion sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The light scenarios can be tailored to your preference at the first installation or during the lifespan of the products. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED gen3 can control up to 6 basic luminaires. Not only will this have a positive impact on your investment, it can also lead to additional energy saving. Mini 300 LED gen3 luminaire is so light that it can be installed effortlessly by one person. Luminaire settings can even be changed from ground level using a smart phone or tablet as a remote control, eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

Product data

General Information		Driver included	Yes
Lamp family code	LED81 [LED module 8100 lm]	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there
Light source replaceable	Yes		
Number of gear units	1 unit		

Mini 300 LED gen3

	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BBP333 [Mini 300 LED gen3]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	7,380 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	155 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Polycarbonate bowl/cover flat
Luminaire light beam spread	113°
Optic type outdoor	Petrol rotational symmetric medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	48 W
Power Factor (Fraction)	0.98
Connection	Push-in connector 5-pole
Cable	Cable without plug 3-pole
Number of products on MCB of 16 A type B	11

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	Internal (no external connection)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	335 mm
Overall width	335 mm
Overall height	92 mm
Effective projected area	0.0314 m ²
Dimensions (Height x Width x Depth)	92 x 335 x 335 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.380) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L97

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BBP333 LED81/740 I PRM
Full product name	BBP333 LED81/740 I PRM
Full product code	871869699754300
Order code	910925865276
Material Nr. (12NC)	910925865276
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696997543
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696997543

Mini 300 LED gen3

Dimensional drawing

