



Mini 300 LED gen3

BBP333 LED159/757 I PAM MDUW MWS

Mini 300 LED gen3, LED module 15900 lm, 757 cool white, Power supply unit with DALI interface, Safety class I, Petrol asymmetric medium, White

Philips Mini 300 LED gen3 luminaires, perfect product design and latest LED technology combination for highly efficient light outputs can turn your petrol station into a branded landmark and help visitors to approach safely in visual comfort. Mini 300 LED gen3, the state-of-the-art LED luminaires with light on demand intelligent motion sensing control system takes energy saving to new levels with dimming, but at the same time, ensuring sufficient lighting for orientation and safety. The light scenarios can be tailored to your preference at the first installation or during the lifespan of the products. The optional Master-Slave combination with a built-in presence and light sensor there's no need for an external sensor and one Master Mini 300 LED gen3 can control up to 6 basic luminaires. Not only will this have a positive impact on your investment, it can also lead to additional energy saving. Mini 300 LED gen3 luminaire is so light that it can be installed effortlessly by one person. Luminaire settings can even be changed from ground level using a smart phone or tablet as a remote control, eliminating the need to work at height. With the free Mini 300 LED App, even the status of the luminaire can be read while standing on the floor. The Mini 300 LED gen3 luminaires in recessed mounted, surface mounted and floodlight versions, which are suitable for undercanopy lighting, is a breakthrough, retrofit solution reduces installation costs.

Product data

General Information		Driver included	Yes
Lamp family code	LED159 [LED module 15900 lm]	Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there
Light source replaceable	Yes		
Number of gear units	1 unit		

Mini 300 LED gen3

	is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BBP333 [Mini 300 LED gen3]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0
Luminous Flux	13,440 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	146 lm/W
Color rendering index (CRI)	70
Light source color	757 cool white
Optical cover type	Polycarbonate bowl/cover flat
Luminaire light beam spread	113°
Optic type outdoor	Petrol asymmetric medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	92 W
Power Factor (Fraction)	0.99
Connection	Push-in connector 5-pole
Cable	Cable without plug 3-pole

Number of products on MCB of 16 A type B 8

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	Internal (no external connection)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	White
Mounting device	-
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	370 mm
Overall width	370 mm
Overall height	170 mm
Effective projected area	0.0584 m²
Dimensions (Height x Width x Depth)	170 x 370 x 370 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.341, 0.329) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L96

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BBP333 LED159/757 I PAM MDUW MWS
Full product name	BBP333 LED159/757 I PAM MDUW MWS
Full product code	871869699785700
Order code	910925865308
Material Nr. (12NC)	910925865308
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696997857
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696997857

Mini 300 LED gen3

Dimensional drawing

