



# CoreLine Malaga LED

## BRP102 LED110/740 I DM

CoreLine Malaga LED, Street light, 83.0 W, 9006 lm, 4000 K, CRI70, Distribution medium, Safety class I, IP65, SRG4-4

The Philips CoreLine Malaga LED family consists of two sizes for urban street lighting. Both feature a Philips LED engine as a light source and a Philips Xitanium driver – a combination that results in energy savings of 50%. CoreLine Malaga LED has been designed to be as efficient as possible. It offers the same performance as the SON-T 50, 70, 100 and 150-W luminaires it replaces, providing the right amount of light in the right place. Furthermore, as the LED light engine in CoreLine Malaga LED will last for the lifetime of the luminaire, it will return your investment simply by saving on the multiple lamp replacements required with SON-T. With its extended gland feature, the CoreLine Malaga LED luminaire is easy to install with no need to open the luminaire to connect the power cable. At the same time, the flat glass cover can be removed to allow access to the driver for maintenance, if required. Special versions of Malaga lighting are available with extra options. However, these specials are manufactured to order only, and have a longer delivery time. The options include: Wide beam (DW) optic, additional surge protection device (10 kV), Marine Salt Protection (MSP) paint finish, Micro Mini Pro photocell 35 Lux, a built-in (glass) 6A fuse, and a 3-metre external flying lead cable (H07RN-F). Not all of these options can always be combined with the others. For more advice, please consult your Philips partner.

### Product data

General information		Remarks
Lamp family code	LED110 [LED module 11000 lm]	* - According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median
Light source replaceable	No	
Number of gear units	Unit	
Driver included	Yes	

## CoreLine Malaga LED

	useful life (B50) value also represents the B10 value.
Light source engine type	LED
Product family code	BRP102 [CoreLine Malaga LED large]
Lighting Technology	LED
Value ladder	Performance
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

### Light Technical

Upwards light output ratio	0
Luminous Flux	9,006 lm
Standard tilt angle post-top	-
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	109 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	-
Optic type outdoor	Distribution medium

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Initial CLO power consumption	N/A W
Average CLO power consumption	N/A W
End CLO power consumption	N/A W
Inrush current	46 A
Inrush time	440 ms
Power Consumption	83.0 W
Power Factor (Fraction)	0.97
Connection	Push-in connector and pull relief
Cable	-
Number of products on MCB of 16 A type B	11

### Temperature

Ambient temperature range	-40 to +35 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	-
Optic material	Polymethyl methacrylate

Optical cover/lens material	Tempered glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Universal for diameter 42 to 60 mm adjustable
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	493 mm
Overall width	217 mm
Overall height	79 mm
Effective projected area	0.22526 m²
Dimensions (height x width x depth)	79 x 217 x 493 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 4 kV differential mode and 4 kV common mode
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.41, 0.39) SDCM ≤5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

### Product Data

Order product name	BRP102 LED110/740 I DM
Full product name	BRP102 LED110/740 I DM
Full EOC	871869699821200
Order code	99821200
Material no. (12 NC)	910925865344
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696998212
Numerator – packs per outer box	1
EAN/UPC - Case	8718696998212

## CoreLine Malaga LED

### Dimensional drawing

