



Maxos fusion

LL646T 9 WH

Maxos fusion Rail - 9 conductors - White

Maxos fusion is an adaptable LED trunking system that offers an excellent quality of light while more than halving energy costs compared to fluorescent lamps. For retail applications, a family of linear panels, non-linear modules and a spot portfolio can be smoothly integrated into the track backbone to let your merchandise sparkle and stand out. For industrial applications, the focus is on reducing installation and maintenance cost by using fewer linear panels. With an electrical set-up of up to 13 wires, the freedom to position these fixtures as required and the integration of other services/third-party hardware, the system allows you to reduce ceiling clutter. It can also be easily re-configured to accommodate future layout changes. The infrastructure is enabled to integrate sensors for data collection, giving you the opportunity to use insightful granular information to support your business.


Product data

General Information	
Light source replaceable	Yes
Driver included	Yes
Connection	CI [Internal connector]
Protection class IEC	Safety class I (I)
Glow-wire test	850/30 [Temperature 850 °C, duration 30 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	ENEC mark
Warranty period	5 years
Material	Steel
RoHS mark	RoHS mark
Angle	-
Accessory colour	White


Product Family Code	LL646T [Maxos fusion Rail]
Operating and Electrical	
Input voltage	220 to 230 V
Input frequency	50 to 60 Hz
Circuit option	9 [9 conductors]
Mechanical and Housing	
Fixation material	Stainless steel
Overall length	4570 mm
Overall width	63 mm
Overall height	44 mm
Colour	White

Maxos fusion

Dimensions (height x width x depth)	44 x 63 x 4570 mm (1.7 x 2.5 x 179.9 in)	Order product name	LL646T 9 WH
Approval and Application		EAN/UPC – product	8718699434571
Ingress protection code	IP54 [Dust accumulation-protected, splash-proof]	Order code	43457199
Mech. impact protection code	IK02 [0.2 J standard]	Numerator – quantity per pack	1
Application Conditions		Numerator – packs per outer box	10
Ambient temperature range	-10 to +35 °C	Material no. (12NC)	910925865348
Product Data		Net weight (piece)	6.010 kg
Full product code	871869943457199		



Dimensional drawing



Maxos Fusion Rail LL512T-LL646T

