



UniStreet

BGS202 LED36/740 I DM 76A

UniStreet Mini, LED module 3600 lm, 740 neutral white, Safety class I, Distribution medium, Side-entry for diameter 76 mm

At relatively low initial cost, the highly efficient LED-based UniStreet luminaire offers significant cost savings compared with conventional street lighting, ensuring full payback within a short period of time. Available in a choice of lumen packages, UniStreet allows point-to-point replacement of outdated conventional light sources and luminaires. The compact, slim luminaire is made of quality recyclable materials. And being a LED solution, it requires little maintenance.

Product data

General Information		EU RoHS compliant		Yes
Lamp family code	LED36 [LED module 3600 lm]	Light Technical		
Light source replaceable	Yes	Upwards light output ratio	0	
Number of gear units	Unit	Luminous Flux	3,222 lm	
Driver included	Yes	Standard tilt angle post-top	0°	
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	Standard tilt angle side entry	0°	
Light source engine type	LED	Correlated Colour Temperature	4000 K	
Product family code	BGS202 [UniStreet Mini]	Luminous efficacy (rated) (nom.)	119 lm/W	
Lighting Technology	LED	Colour rendering index (CRI)	70	
CE mark	Yes	Light source colour	740 neutral white	
Warranty period	5 years	Optical cover type	Flat glass	
Flammability mark	For mounting on normally flammable surfaces	Luminaire light beam spread	74° x 74°	
ENEC mark	ENEC mark	Optic type outdoor	Distribution medium	
		Operating and Electrical		
		Input Voltage	230 V	

Line Frequency	50 to 60 Hz
Initial CLO power consumption	[DELETE] W
Average CLO power consumption	[DELETE] W
End CLO power consumption	[DELETE] W
Inrush current	27 A
Inrush time	0.265 ms
Power Consumption	27 W
Power Factor (Fraction)	0.92
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	18

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------


Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Side-entry for diameter 76 mm
Optical cover/lens shape	Curved
Optical cover/lens finish	Clear
Overall length	505 mm
Overall width	270 mm
Overall height	98 mm

Dimensional drawing



Overall diameter	0 mm
Effective projected area	0.038 m²
Dimensions (height x width x depth)	98 x 270 x 505 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge-protection level
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.50 %
------------------------------------	--------

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	BGS202 LED36/740 I DM 76A
Full product name	BGS202 LED36/740 I DM 76A
Full EOC	871869698810700
Order code	98810700
Material no. (12 NC)	910925866150
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696988107
Numerator – packs per outer box	1
EAN/UPC – Case	8718696988107

