



DigiStreet

BGP762 LED110-/740 I DN10 DGR 32-48

DigiStreet Medium, LED module 11000 lm, 740 neutral white, Safety class I, Distribution narrow 10, Dark gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Spigot for diameter 32 to 48 mm

Developed with the aim to become your long term partner „ the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the Philips CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information		Lighting Technology	
Lamp family code	LED110 [LED module 11000 lm]	Value ladder	Specification
Light source replaceable	Yes	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	-
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	ENEC mark	ENEC mark
Light source engine type	LED	EU RoHS compliant	Yes
Product family code	BGP762 [DigiStreet Medium]	Light Technical	
		Upward light output ratio	0

Luminous Flux	10,010 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	164 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	68° x 158°
Optic type outdoor	Distribution narrow 10

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	61 W
Power Factor (Fraction)	0.98
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 32 to 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	860 mm
Overall width	361 mm

Overall height	107 mm
Effective projected area	0.068 m²
Dimensions (Height x Width x Depth)	107 x 361 x 860 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38. 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L97

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP762 LED110-/740 I DN10 DGR 32-48
Full product name	BGP762 LED110-/740 I DN10 DGR 32-48
Full product code	871869637826700
Order code	37826700
Material Nr. (12NC)	910925866224
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696378267
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696378267

Dimensional drawing

