



# DigiStreet

## BGP761 LED59-/830 II DN11 DGR D11 62

DigiStreet Mini, LED module 5900 lm, 830 warm white, Safety class II, Distribution narrow 11, Dark gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Spigot for diameter 62 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

### Product data

General Information	
Lamp family code	LED59 [LED module 5900 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BGP761 [DigiStreet Mini]

Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical	
Upward light output ratio	0

Luminous Flux	5,400 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	132 lm/W
Color rendering index (CRI)	80
Light source color	830 warm white
Optical cover type	Flat glass
Luminaire light beam spread	53° x 71°
Optic type outdoor	Distribution narrow 11

#### Operating and Electrical

Input Voltage	220–240 V
Line Frequency	50 to 60 Hz
Inrush current	46 A
Inrush time	0.25 ms
Power Consumption	41 W
Power Factor (Fraction)	0.97
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	11

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit regulating external
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 62 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	860 mm
Overall width	236 mm

Overall height	107 mm
Effective projected area	0.0666 m²
Dimensions (Height x Width x Depth)	107 x 236 x 860 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.43. 0.40) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L97

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

#### Product Data

Order product name	BGP761 LED59-/830 II DN11 DGR D11 62
Full product name	BGP761 LED59-/830 II DN11 DGR D11 62
Full product code	871869637696600
Order code	37696600
Material Nr. (12NC)	910925866240
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696376966
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696376966

Dimensional drawing

