



# DigiStreet

## BGP762 LED210-/740 II DX70 DGR 76

DigiStreet Medium, LED module 21000 lm, 740 neutral white, Safety class II, Distribution extra wide 70, Dark gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Spigot for diameter 76 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

### Product data

General Information	
Lamp family code	LED210 [LED module 21000 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BGP762 [DigiStreet Medium]

Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical	
Upward light output ratio	0

Luminous Flux	18,060 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	151 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	106° x 86°
Optic type outdoor	Distribution extra wide 70

#### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	120 W
Power Factor (Fraction)	0.99
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	8

#### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

#### Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

#### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 76 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	917 mm
Overall width	361 mm

Overall height	107 mm
Effective projected area	0.068 m²
Dimensions (Height x Width x Depth)	107 x 361 x 917 mm

#### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

#### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38. 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

#### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L96

#### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

#### Product Data

Order product name	BGP762 LED210-/740 II DX70 DGR 76
Full product name	BGP762 LED210-/740 II DX70 DGR 76
Full product code	871869637837300
Order code	37837300
Material Nr. (12NC)	910925866246
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696378373
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696378373

Dimensional drawing

