



DigiStreet

BGP763 LED260-/740 I DX10 DGR 32-48

DigiStreet Large, LED module 26000 lm, 740 neutral white, Safety class I, Distribution extra wide 10, Dark gray, Luminaire surge protection level until 6 kV differential mode and 8 kV common mode, Spigot for diameter 32 to 48 mm

Developed with the aim to become your long term partner „ the system ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come!. Its two sockets enable you to connect directly to the Philips CityTouch system and is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain an optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information	
Lamp family code	LED260 [LED module 26000 lm]
Light source replaceable	Yes
Number of gear units	2 units
Driver included	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BGP763 [DigiStreet Large]

Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC mark
EU RoHS compliant	Yes

Light Technical	
Upward light output ratio	0

Luminous Flux	22,100 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	147 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	150° - 43° x 67°
Optic type outdoor	Distribution extra wide 10

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	150 W
Power Factor (Fraction)	0.99
Connection	Screw connector
Cable	-
Number of products on MCB of 16 A type B	4

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Spigot for diameter 32 to 48 mm
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	1,011 mm
Overall width	361 mm

Overall height	121 mm
Effective projected area	0.08 m²
Dimensions (Height x Width x Depth)	121 x 361 x 1011 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L96

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP763 LED260-/740 I DX10 DGR 32-48
Full product name	BGP763 LED260-/740 I DX10 DGR 32-48
Full product code	871869637840300
Order code	37840300
Material Nr. (12NC)	910925866250
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696378403
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696378403

Dimensional drawing

