



Luma gen2

BGP702 LW10 LED50-4S/830 DM11 GF CTGO

LUMA GEN2 MICRO, LED module 5000 lm, LED, 40.5 W, Power supply unit with DALI and SystemReady interface, Distribution medium 11, Glass, 70° x 37°, GPRS network, Post-top for diameter 60 to 76 mm

Luma gen2 is the next generation of the Luma LED luminaire family, fully optimised to become your long-term lighting and innovation partner. While keeping the distinctive design characteristics of the first generation, Luma gen2 gives you the benefits of the latest technologies thanks to its future-proof System Ready architecture, use of optimised Ledgine LED and optical platform ensuring best-in-class lighting performance in a broad range of applications. It also offers improved serviceability. Installation has also become easier and faster, and thanks to the Service tag, you have access to all relevant documentations onsite. Also, the cable feed-through has been redesigned and access to the gear components is easy thanks to top down tool-less access. Luma gen2 also offers all connectivity and dimming options available today and thanks to being System Ready, it can also to be paired with lighting management systems such as Interact City or existing and upcoming sensor innovations. The Luma gen2 has been developed to optimise and simplify spare part repair and maintenance work using a new plug-and-play GearFlex module containing all electrical components in an easy to handle and accessible box inside the housing. As a company conscious about the impact of light on the environment and biodiversity, we also equipped the Luma gen2 with dedicated light recipes that help with maintaining the optimal ecosystems for bats or preserve a dark night sky.

Product data

General Information	
Lamp family code	LED50 [LED module 5000 lm]

Light source replaceable	Yes
Number of gear units	Unit

Luma gen2

Driver included	Yes
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED
Product family code	BGP702 [LUMA GEN2 MICRO]
Lighting Technology	LED
Value ladder	Specification
CE mark	Yes
Warranty period	5 years
Flammability mark	-
ENEC mark	ENEC plus mark
EU RoHS compliant	Yes

Light Technical

Upwards light output ratio	0
Luminous Flux	4,500 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	-
Correlated Colour Temperature	3000 K
Luminous efficacy (rated) (nom.)	111 lm/W
Colour rendering index (CRI)	>80
Light source colour	830 warm white
Optical cover type	Glass
Luminaire light beam spread	70° x 37°
Optic type outdoor	Distribution medium 11

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.3 ms
Power Consumption	40.5 W
Power Factor (Fraction)	0.98
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	21

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI and SystemReady interface
Control interface	GPRS network
Constant light output	No

Mechanical and Housing

Housing material	Aluminium die cast
Reflector material	-
Optic material	Polymethyl methacrylate

Optical cover/lens material	Glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Post-top for diameter 60 to 76 mm
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	560 mm
Overall width	295 mm
Overall height	245 mm
Effective projected area	0.094 m²
Dimensions (height x width x depth)	245 x 295 x 560 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.434, 0.403) SDCM 5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5,000 hours	0.005 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L96

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	Not applicable

Product Data

Order product name	BGP702 LW10 LED50-4S/830 DM11 GF CTGO
Full product name	BGP702 LW10 LED50-4S/830 DM11 GF CTGO
Full EOC	871951405968900
Order code	05968900
Material no. (12 NC)	910925866536
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514059689
Numerator – packs per outer box	1
EAN/UPC - Case	8719514059689

Luma gen2

Dimensional drawing

