



LumiStreet gen2

BGP292 LED75-4S/740 I DX10 7024 D9 76S

LumiStreet gen2 Mini, LED module 7500 lm, 740 neutral white, Safety class I, Distribution extra-wide 10, Side-entry for diameter 76 mm

Increasing numbers of municipalities are having to upgrade large-scale conventional street lighting installations with energy-efficient LED technology. But they are having to do this with smaller and smaller budgets. That's why the new generation of LumiStreet has been upgraded and designed to provide a solution to this challenge, it is the ideal solution for performing point-to-point replacement of conventional lighting. LumiStreet gen2 achieves this by offering high-efficiency, low Total Cost of Ownership and ease of installation and maintenance. The ease of installation and maintenance is enabled by the Philips Service tag. Moreover, the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City.

Product data

General Information			
Lamp family code	LED75 [LED module 7500 lm]	CE mark	Yes
Light source replaceable	Yes	Warranty period	5 years
Number of gear units	Unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC plus mark
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	EU RoHS compliant	Yes
Light source engine type	LED	Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BGP292 [LumiStreet gen2 Mini]		
Lighting Technology	LED		
Value ladder	Specification		

LumiStreet gen2

Light Technical	
Upwards light output ratio	0
Luminous Flux	6,612 lm
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°
Correlated Colour Temperature	4000 K
Luminous efficacy (rated) (nom.)	150 lm/W
Colour rendering index (CRI)	70
Light source colour	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	150° - 43° x 67°
Optic type outdoor	Distribution extra-wide 10
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	47 A
Inrush time	0.25 ms
Power Consumption	44 W
Power Factor (Fraction)	0.98
Connection	2 push-in connectors 5-pole
Cable	-
Number of products on MCB of 16 A type B	10
Temperature	
Ambient temperature range	-40 to +50 °C
Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No
Mechanical and Housing	
Housing material	Aluminium die cast
Reflector material	Polycarbonate
Optic material	Polymethyl methacrylate
Optical cover/lens material	Glass
Fixation material	Aluminium
Housing Colour	Grey
Mounting device	Side-entry for diameter 76 mm
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear

Overall length	620 mm
Overall width	234 mm
Overall height	95 mm
Effective projected area	0.0251 m²
Dimensions (height x width x depth)	95 x 234 x 620 mm
Approval and Application	
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2
Over Time Performance (IEC Compliant)	
Driver failure rate at 5,000 hours	0.5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L97
Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)
Product Data	
Order product name	BGP292 LED75-4S/740 I DX10 7024 D9 76S
Full product name	BGP292 LED75-4S/740 I DX10 7024 D9 76S
Full EOC	871951407970000
Order code	07970000
Material no. (12 NC)	910925866705
SAP numerator – quantity per pack	1
EAN/UPC — Product/Case	8719514079700
Numerator – packs per outer box	1
EAN/UPC – Case	8719514079700

Dimensional drawing

