



# UniStreet gen2

## BGP282 LED70-4S/740 I DN10 48/60S

UniStreet gen2 Mini, LED module 7000 lm, 740 neutral white, Safety class I, Distribution narrow 10, Side-entry for diameter 48 to 60 mm

Designed for large-scale ledification projects, the UniStreet gen2 is the ideal 1:1 luminaire replacement for municipalities. Thanks to its high efficiency and low initial cost, the UniStreet gen2 luminaire enables a fast payback and significant savings in terms of energy consumption within a short period of time. The ease of installation and maintenance is enabled by the Philips Service tag and the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City. Available with a number of different optics and lumen packages that can even be tuned further to fit exact project requirements, UniStreet gen2 is a true point-to-point replacement solution for conventional light sources. The compact luminaire, using high-quality materials is also easy to dismantle and recycle at the end of its lifetime.

### Product data

General Information		Lighting Technology	LED
Lamp family code	LED70 [LED module 7000 lm]	Value ladder	Specification
Light source replaceable	Yes	CE mark	Yes
Number of gear units	1 unit	Warranty period	5 years
Driver included	Yes	Flammability mark	For mounting on normally flammable surfaces
Remarks	* At extreme ambient temperatures the luminaire might automatically dim down to protect components	ENEC mark	ENEC plus mark
Light source engine type	LED	EU RoHS compliant	Yes
Service tag	Yes	Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection
Product family code	BGP282 [UniStreet gen2 Mini]		

UniStreet gen2

	device, optics, front cover and mechanical parts
--	--

Light Technical

Upward light output ratio	0
Luminous Flux	6,090 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	150 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	68° x 158°
Optic type outdoor	Distribution narrow 10

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	47 A
Inrush time	0.25 ms
Power Consumption	40.5 W
Power Factor (Fraction)	0.98
Connection	2 Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	10

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit regulating
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Gray
Mounting device	Side-entry for diameter 48 to 60 mm

Optical cover shape	Flat
Optical cover finish	Clear
Overall length	620 mm
Overall width	234 mm
Overall height	95 mm
Effective projected area	0.0251 m²
Dimensions (Height x Width x Depth)	95 x 234 x 620 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L97

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	0% (digital)

Product Data

Order product name	BGP282 LED70-4S/740 I DN10 48/60S
Full product name	BGP282 LED70-4S/740 I DN10 48/60S
Full product code	871951410019000
Order code	910925866754
Material Nr. (12NC)	910925866754
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514100190
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514100190

UniStreet gen2

Dimensional drawing

