



# GentleSpace gen2

## BY471P GRN170S/840 PSD HRO PC BR SI

GentleSpace 2, LED GreenLine system flux 17000 lm, 840 neutral white, Power supply unit with DALI interface, High-rack optic, Polycarbonate bowl/cover, Silver

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

### Product data

<b>General Information</b>			
Lamp family code	GRN170S [LED GreenLine system flux 17000 lm]		useful life (B50) value also represents the B10 value.
Cap base	- [-]	<b>Product family code</b>	BY471P [GentleSpace 2]
Light source replaceable	Yes	<b>Lighting Technology</b>	LED
Number of gear units	Unit	<b>Embedded control</b>	-
Gear	EB [Electronic]	<b>CE mark</b>	Yes
Driver included	Yes	<b>Warranty period</b>	5 years
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median	<b>Flammability mark</b>	For mounting on easily flammable surfaces
		<b>ENEC mark</b>	ENEC mark
		<b>Glow-wire test</b>	Temperature 850 °C, duration 5 s
		<b>EU RoHS compliant</b>	Yes
		<b>Light Technical</b>	
		<b>Luminous Flux</b>	17,000 lm
		<b>Correlated Colour Temperature</b>	4000 K

## GentleSpace gen2

Luminous efficacy (rated) (nom.)	155 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	114 degree(s)
Light source colour	840 neutral white
Optic type	High-rack optic
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	16° x 47°
Unified Glare Rating (CEN)	Not applicable

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	110 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of products on MCB of 16 A type B	12

### Temperature

Ambient temperature range	-30 to +45 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Polymethyl methacrylate
Fixation material	Steel
Housing Colour	Silver
Optical cover/lens finish	Clear
Overall length	600 mm
Overall width	450 mm

Overall height	150 mm
Dimensions (height x width x depth)	150 x 450 x 600 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.38, 0.38) SDCM <3
Power consumption tolerance	+/-11%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L85
Lumen maintenance at median useful life* 100,000 h	L70

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	No

### Product Data

Order product name	BY471P GRN170S/840 PSD HRO PC BR SI
Full product name	BY471P GRN170S/840 PSD HRO PC BR SI
Full EOC	871869632215400
Order code	32215400
Material no. (12 NC)	910930205974
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696322154
Numerator – packs per outer box	1
EAN/UPC – Case	8718696322154

## GentleSpace gen2

### Dimensional drawing

