



# **GentleSpace gen2**

### BY471P GRN170S/840 PSD HRO GC BR WH

GentleSpace 2, LED GreenLine system flux 17000 lm, 840 neutral white, Power supply unit with DALI interface, High-rack optic, Clear glass, White

With the introduction of the GentleSpace LED luminaire in 2011, Philips achieved a breakthrough in high-bay lighting, offering a huge reduction in power consumption, a long service life and an innovative design. Now, with GentleSpace gen2, Philips is setting a new standard in the market, with an improved total cost of ownership, even in extreme conditions. In addition, a high diversity of options are available to ensure an ideal solution for your application like optics, coatings and enabling the use of a central emergency grid (PSED).

#### **Product data**

General Information	
Lamp family code	GRN170S [LED GreenLine system flux 17000
	lm]
Cap base	- [-]
Light source replaceable	Yes
Number of gear units	Unit
Gear	EB [Electronic]
Driver included	Yes
Remarks	*- According to the Lighting Europe guidance
	paper 'Evaluating performance of LED based
	luminaires – January 2018': statistically there
	is no relevant difference in lumen
	maintenance between the B50 and, for
	example, the B10. Therefore, the median

	useful life (B50) value also represents the
	B10 value.
Product family code	BY471P [GentleSpace 2]
Lighting Technology	LED
Embedded control	-
CE mark	Yes
Warranty period	5 years
Flammability mark	For mounting on easily flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 5 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	17,000 lm
Correlated Colour Temperature	4000 K

Datasheet, 2023, April 29 data subject to change

## GentleSpace gen2

Luminous efficacy (rated) (nom.)	155 lm/W
Colour rendering index (CRI)	≥80
Beam angle of light source	114 degree(s)
Light source colour	840 neutral white
Optic type	High-rack optic
Optical cover type	Clear glass
Luminaire light beam spread	16° x 47°
Unified Glare Rating (CEN)	Not applicable
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	4.8 A
Inrush time	2.3 ms
Power Consumption	110 W
Power Factor (Fraction)	0.9
Connection	External connector
Cable	Cord with plug Wieland/Adels compatible 5
	pole
Number of products on MCB of 16 A type B	12
Temperature	
Ambient temperature range	-30 to +45 °C
Controls and Dimming	
Dimmable	
	Yes
Driver/power unit/transformer	
Driver/power unit/transformer  Control interface	Power supply unit with DALI interface
Driver/power unit/transformer  Control interface  Constant light output	
Control interface	Power supply unit with DALI interface DALI
Control interface	Power supply unit with DALI interface DALI
Control interface  Constant light output	Power supply unit with DALI interface DALI
Control interface Constant light output Mechanical and Housing	Power supply unit with DALI interface  DALI  No
Control interface Constant light output  Mechanical and Housing Housing material	Power supply unit with DALI interface  DALI  No
Control interface Constant light output  Mechanical and Housing Housing material Reflector material	Power supply unit with DALI interface DALI No Aluminium
Control interface Constant light output  Mechanical and Housing Housing material Reflector material Optic material	Power supply unit with DALI interface DALI No Aluminium - Acrylate
Control interface Constant light output  Mechanical and Housing Housing material Reflector material Optic material Optical cover/lens material	Power supply unit with DALI interface  DALI  No  Aluminium  -  Acrylate  Glass
Control interface Constant light output  Mechanical and Housing Housing material Reflector material Optic material Optical cover/lens material Fixation material	Power supply unit with DALI interface DALI No Aluminium - Acrylate Glass Steel
Control interface Constant light output  Mechanical and Housing Housing material Reflector material Optic material Optical cover/lens material Fixation material Housing Colour	Power supply unit with DALI interface DALI No  Aluminium - Acrylate Glass Steel White

Overall height	150 mm	
Dimensions (height x width x depth)	150 x 450 x 600 mm	
Approval and Application		
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]	
Mech. impact protection code	IK07 [2 J reinforced]	
Protection class IEC	Safety class I	
Initial Performance (IEC Compliant)		
Luminous flux tolerance	+/-7%	
Initial chromaticity	(0.38, 0.38) SDCM <3	
Power consumption tolerance	+/-11%	
Over Time Performance (IEC Compliant)		
Control gear failure rate at median useful	5 %	
life 50,000 h		
Control gear failure rate at median useful	10 %	
life 100,000 h		
Lumen maintenance at median useful life	' L85	
50,000 h		
Lumen maintenance at median useful life	' L70	
100,000 h		
Application Conditions		
Performance ambient temperature Tq	25 ℃	
Maximum dim level	10%	
Suitable for random switching	No	
Product Data		
Order product name	BY471P GRN170S/840 PSD HRO GC BR WH	
Full product name	BY471P GRN170S/840 PSD HRO GC BR WH	
Full EOC	871869632241300	
Order code	32241300	
Material no. (12 NC)	910930206001	
SAP numerator – quantity per pack	1	
EAN/UPC — Product/Case	8718696322413	
Numerator – packs per outer box	1	
EAN/UPC - Case	8718696322413	

### GentleSpace gen2

#### Dimensional drawing





