



# LED Wall Mount

## BWS150 LED200/WW PSU 220-240V 7043

LED Low Power, Power supply unit (On/Off)

People want to create a pleasant atmosphere around their property – something that will catch visitors’ attention, make them feel good and want to come back again. They would like to be able to create an appealing ambience at minimum cost, though without compromising on the quality of the lighting. Combining a simple round design with reliable lighting performance, this low-cost white-light LED wall fixture with opal diffuser delivers a soft light effect with attractive uniformity.

### Product data

General Information	
Lamp family code	LED-LP [LED Low Power]
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	1 years
Flammability mark	For mounting on normally flammable surfaces
Light Technical	
Luminous Flux	240 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	41.38 lm/W
Color rendering index (CRI)	>80
Number of light sources	96
Light source color	830 warm white

Optical cover type	Polycarbonate bowl/cover UV-resistant
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	5.8 W
Power Factor (Fraction)	0.4
Connection	Screw connection block
Cable	Cable without plug 2-pole
Number of products on MCB of 16 A type B 1	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-

## LED Wall Mount

Constant light output	No
<b>Mechanical and Housing</b>	
Housing Material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Dark gray
Mounting device	Allen screw fixation
Optical cover finish	Matte
Overall height	62 mm
Overall diameter	200 mm
<b>Approval and Application</b>	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class II

<b>Initial Performance (IEC Compliant)</b>	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	BWS150 LED200/WW PSU 220-240V 7043
Full product name	BWS150 LED200/WW PSU 220-240V 7043
Full product code	911401178880
Order code	911401178880
Material Nr. (12NC)	911401178880
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291995470
Numerator - Packs per outer box	24

### Dimensional drawing

