



GreenUp Highbay G2

BY560P LED210/NW PSD/CL WB

840 neutral white - Power supply unit with DALI interface - Wide beam

Height is not an issue any more, maximum 16 m movement detection together with the wireless ZigBee control, GreenUp HighBay G2, light up your space smartly.

Product data

General Information	
Beam angle of light source	- °
Light source colour	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optic type	WB [Wide beam]
Optical cover/lens type	LIN-PC [Linear-lens array in polycarbonate cover]
Luminaire light beam spread	90°
Control interface	DALI
Connection	Flying leads/wires
Cable	Cable 1.5 m without plug (CIK5)
Protection class IEC	Safety class I (I)
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Constant light output	No
Number of products on MCB	24

LED engine type	LED
Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Inrush current	5.1 A
Inrush time	760 ms
Power factor (min.)	0.95
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Housing material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall length	525 mm
Overall width	280 mm

GreenUp Highbay G2

Colour	Aluminum and white
--------	--------------------

Approval and Application

Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]

Initial Performance (IEC Compliant)

Initial luminous flux	21000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	137 lm/W
Init. Corr. Colour Temperature	4000 K
Init. Color rendering index	>80
Initial chromaticity	(0.38,0.38)SDCM<5
Initial input power	153 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	65000 h
Median useful life L80B50	45000 h


Median useful life L90B50	25000 h
---------------------------	---------

Application Conditions


Ambient temperature range	-20 to +45 °C
Maximum dimming level	1% (depends on dimmer, ELV)
Suitable for random switching	No

Product Data

Full product code	911401507551
Order product name	BY560P LED210/NW PSD/CL WB
Order code	01507551
Numerator – quantity per pack	1
Numerator – packs per outer box	2
Material no. (12NC)	911401507551
Net weight (piece)	3.449 kg



Dimensional drawing



GreenUp High-bay BY550P/BY550X

