



# GreenPerform Highbay G4

## BY698P LED265/NW PSU NB GM G2

GreenPerform Highbay G4, 192 W, 26500 lm, 4000 K, 60°

Following the success of GreenPerform Highbay families, GreenPerform Highbay G4 is continuously exploring a better price & performance balance. The product family offers wide product ranges, competitive enough SPEC with long term quality & reliability, covering most of the potential industrial applications.

### Product data

General Information	
Light source replaceable	No
Number of gear units	2 units
Driver included	Yes
Light source engine type	LED
Service tag	Yes
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	26,500 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	135 lm/W

Color rendering index (CRI)	>80
Light source color	840 neutral white
Optic type	Symmetrical
Optical cover type	Polycarbonate bowl/cover
Luminaire light beam spread	60°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	64 A
Inrush time	0.75 ms
Power Consumption	192 W
Power Factor (Fraction)	0.95
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	8

# GreenPerform Highbay G4

## Temperature

Ambient temperature range	-30 to +50 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

## Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Gray
Optical cover finish	Clear
Overall height	99 mm
Overall diameter	416 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Protection class IEC	Safety class I

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

## Application Conditions

Maximum dim level	Not applicable
Suitable for random switching	No

## Product Data

Order product name	BY698P LED265/NW PSU NB GM G2
Full product name	BY698P LED265/NW PSU NB GM G2
Full product code	872016954898500
Order code	911401518461
Material Nr. (12NC)	911401518461
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169548985
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169548985

## Dimensional drawing

