

GreenUp Highbay G2

BY560X LED210/NW ACW2 IS HRO CAU

GreenUp Highbay G2, 153 W, 21000 lm, 4000 K, DALI, 45° x 90°

Height is not an issue any more, maximum 16m movement detection together with the wireless ZigBee control, GreenUp HighBay G2,light up your space smartly.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
CE mark	CE mark
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	-
Glow-wire test	Temperature 650 °C, duration 5 s

Light Technical	
Luminous Flux	21,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	137 lm/W
Color rendering index (CRI)	>80
Beam angle of light source	- degree(s)
Light source color	840 neutral white
Optic type	High-rack optic
Optical cover type	Linear-lens array in polycarbonate cover
Luminaire light beam spread	45° x 90°

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	5.1 A
Inrush time	760 ms
Power Consumption	153 W
Power Factor (Fraction)	0.95
Connection	-
Cable	Cable 3.0 m with plug
Number of products on MCB of 16 A type B	24

GreenUp Highbay G2

Temperature	
Ambient temperature range	-20 to +45 °C

Controls and Dimming	
Dimmable	Wireless Dim
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	-
Housing Color	Aluminum and white
Optical cover finish	Clear
Overall length	670 mm
Overall width	280 mm

Approval and Application	
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class I


Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38.0.38)SDCM<5
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	65,000 hour(s)
Median useful life L80B50	45,000 hour(s)
Median useful life L90B50	25,000 hour(s)

Application Conditions	
Maximum dim level	1%
Suitable for random switching	Yes

Product Data	
Order product name	BY560X LED210/NW ACW2 IS HRO CAU
Full product name	BY560X LED210/NW ACW2 IS HRO CAU
Full product code	911401520251
Order code	911401520251
Material Nr. (12NC)	911401520251
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.