



LuxSpace G4

DN588B LED6/830 PSU C D100 WH WB GC

LuxSpace G4, 6.6 W, 670 lm, 3000 K, Facetted reflector with beam angle 60°, Textured, Finger-protected

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury looking

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	CE mark
Warranty period	3 years
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	670 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	102 lm/W
Color rendering index (CRI)	>80
Light source color	830 warm white
Optic type	Facetted reflector with beam angle 60°
Optical cover type	Reflector

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	5.2 A
Inrush time	0.23 ms
Power Consumption	6.6 W
Power Factor (Fraction)	0.9
Connection	Push-in connector with 2 poles and pull relief
Number of products on MCB of 16 A type B 34	
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit external (On/Off)
Control interface	-
Constant light output	No

LuxSpace G4

Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Optical cover finish	Textured
Overall length	0 mm
Overall width	0 mm
Overall height	68 mm
Overall diameter	112 mm
Dimensions (Height x Width x Depth)	68 x 0 x 0 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	1 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	21,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	DN588B LED6/830 PSU C D100 WH WB GC
Full product name	DN588B LED6/830 PSU C D100 WH WB GC
Full product code	911401536641
Order code	911401536641
Material Nr. (12NC)	911401536641
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

