



Mini500 G3

BCP500 G2 LED180/NW PSU A-WB

840 neutral white - Wide beam

The Mini 500 G3 is designed for petrol-station canopies and low/high-bay applications, this ultra-efficient retrofit fixture offers outstanding light quality, effective thermal management and a long lifespan. For further energy savings, you could select either simple movement-detector sensor or movement detection combined with a daylight sensor.

Product data

General Information	
Lamp colour code	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	WB [Wide beam]
Optical cover/lens type	GT [Tempered glass]
Luminaire light beam spread	83° x 110°
Control interface	-
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Protection class IEC	Safety class I (I)
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	F [For mounting on normally flammable surfaces]
CE mark	CE mark
ENEC mark	-
Warranty period	3 years
Constant light output	No
Number of products on MCB	4

LED engine type	LED
-----------------	-----

Operating and Electrical	
Input voltage	220 to 240 V
Input frequency	50 to 60 Hz
Power factor (min.)	0.95

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Housing material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Tempered glass
Fixation material	-
Optical cover/lens finish	Clear
Overall length	335 mm
Overall width	335 mm

Mini500 G3

Colour	White
--------	-------

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK07 [2 J reinforced]

Initial Performance (IEC Compliant)

Initial luminous flux	18000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	129 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>80
Initial chromaticity	(0.38.0.38)SDCM<5
Initial input power	140 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50000 h
Median useful life L80B50	40000 h


Median useful life L90B50	30000 h
---------------------------	---------

Application Conditions


Ambient temperature range	-40 to +45 °C
Maximum dimming level	Not applicable
Suitable for random switching	No

Product Data

Full product code	911401537451
Order product name	BCP500 G2 LED180/NW PSU A-WB
Order code	911401537451
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	911401537451
Net weight (piece)	8.099 kg



Dimensional drawing



Mini500 G2 BBP500/BCP500/BGP500

