



Truefashion Projector GCGM

ST700T LED20 930PC PSU NB 1C BK

Truefashion Projector GCGM, 22.3 W, 930 warm white, 15°, Finger-protected

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Warnings and Safety

- 3 years

Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	-
CE mark	CE mark
Warranty period	3 years
ENEC mark	-
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	1,604.8 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	72.1 lm/W

Color rendering index (CRI)	>90
Beam angle of light source	120 degree(s)
Light source color	930 warm white
Optic type	Beam angle 15°
Optical cover type	Lens
Luminaire light beam spread	15°
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	22.3 W
Power Factor (Fraction)	0.9
Connection	Track
Cable	-

Truefashion Projector GCGM

Number of products on MCB of 16 A type B	-
Temperature	
Ambient temperature range	-20 to +35 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Black
Optical cover finish	Clear
Overall length	164 mm
Overall height	185 mm
Overall diameter	66 mm
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.422, 0.386) SDCM<3
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.14 %
Median useful life L70B50	50,000 hour(s)
Median useful life L80B50	50,000 hour(s)
Median useful life L90B50	32,600 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Suitable for random switching	No
Product Data	
Order product name	ST700T LED20 930PC PSU NB 1C BK
Full product name	ST700T LED20 930PC PSU NB 1C BK
Full product code	911401546961
Order code	911401546961
Material Nr. (12NC)	911401546961
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing



