



# LuxSpace G4

## DN589B LED10/840 PSD C D150 WH WB WP CAU

LuxSpace G4, 10.5 W, 1000 lm, 4000 K, DALI, Facetted reflector with beam angle 60°, Textured, Finger-protected; dust accumulation-protected, splash-proof

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury looking

### Product data

<b>General Information</b>		<b>Optical cover type</b>	
Light source replaceable	No	Reflector	
Number of gear units	1 unit	<b>Operating and Electrical</b>	
Driver included	Yes	Input Voltage	220 to 240 V
Light source engine type	LED	Line Frequency	50 or 60 Hz
CE mark	CE mark	Inrush current	16 A
Warranty period	3 years	Inrush time	0.22 ms
Flammability mark	For mounting on normally flammable surfaces	Power Consumption	10.5 W
Glow-wire test	Temperature 650 °C, duration 30 s	Power Factor (Fraction)	0.9
EU RoHS compliant	Yes	Connection	Connector with 2 additional wires for light regulation
<b>Light Technical</b>		Number of products on MCB of 16 A type B 24	
Luminous Flux	1,000 lm	<b>Temperature</b>	
Correlated Color Temperature (Nom)	4000 K	Ambient temperature range	-20 to +40 °C
Luminous Efficacy (rated) (Nom)	119 lm/W	<b>Controls and Dimming</b>	
Color rendering index (CRI)	>80	Dimmable	Yes
Light source color	840 neutral white	Driver/power unit/transformer	Power supply unit external (On/Off)
Optic type	Facetted reflector with beam angle 60°	Control interface	DALI

LuxSpace G4

Constant light output	No
-----------------------	----

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	Polycarbonate aluminum coated
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White and black
Optical cover finish	Textured
Overall length	0 mm
Overall width	0 mm
Overall height	100 mm
Overall diameter	162 mm
Dimensions (Height x Width x Depth)	100 x 0 x 0 mm

Approval and Application

Ingress protection code	IP20/54 [Finger-protected; dust accumulation-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	1 %
Median useful life L70B50	50,000 h
Median useful life L80B50	50,000 h
Median useful life L90B50	21,000 h

Application Conditions

Maximum dim level	1%
-------------------	----

Product Data

Order product name	DN589B LED10/840 PSD C D150 WH WB WP CAU
Full product name	DN589B LED10/840 PSD C D150 WH WB WP CAU
Full product code	911401553541
Order code	911401553541
Material Nr. (12NC)	911401553541
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

