



GreenPerform Waterproof G3

WT198C LED60S/840 IAI L1500

Power supply unit - - - - 114°

GreenPerform Waterproof G3 provides excellent optics with reliable performance, easy installation and maintenance

Product data

General Information	
Beam angle of light source	120 °
Lamp colour code	840 neutral white
Light source replaceable	No
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Optic type	No [-]
Optical cover/lens type	No [-]
Luminaire light beam spread	114°
Control interface	-
Connection	No [-]
Cable	-
Protection class IEC	Safety class I (I)
Glow-wire test	850/30 [Temperature 850 °C, duration 30 s]
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	-
Constant light output	Programmable
Number of products on MCB	24

EU RoHS compliant	No
LED engine type	LED

Operating and Electrical

Input voltage	220 to 240 V
Input frequency	50 or 60 Hz
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	22 A
Inrush time	270 ms
Power factor (min.)	0.9

Mechanical and Housing

Housing material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Stainless steel
Optical cover/lens finish	Opal
Overall length	1515 mm

GreenPerform Waterproof G3

Overall width	80 mm
Overall height	85 mm
Overall diameter	80 mm
Colour	Grey

Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]

Initial Performance (IEC Compliant)

Initial luminous flux	6000 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	140 lm/W
Lamp colour temperature	4000 K
Colour Rendering Index	>80
Initial chromaticity	(0.38,0.38)
Initial input power	42.7 W
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L70B50	50000 h
---------------------------	---------


Median useful life L80B50	42000 h
Median useful life L90B50	20000 h

Application Conditions


Ambient temperature range	-25 to +40 °C
Maximum dimming level	Not applicable
Suitable for random switching	Not applicable

Product Data

Full product code	911401562661
Order product name	WT198C LED60S/840 IAI L1500
Order code	911401562661
Numerator – quantity per pack	1
Numerator – packs per outer box	9
Material no. (12NC)	911401562661
Net weight (piece)	1.700 kg



Dimensional drawing



WT188C/WL020C

