



# SmartBright Highbay G3

## BY239P LED100/NW PSU

SmartBright Highbay G3, 97 W, 10000 lm, 4000 K, 100°

SmartBright Highbay G3 is a high efficient and reliable LED luminaire. Designed as the point to point replacement for HPI 250W/400W luminaires, it offers customers all the benefits of LED lighting – reduced energy consumption, longer service time and less maintenance. In addition, with using high quality of the optical cover, it provides an excellent quality of light, which effectively improves the comfort of your environment.

### Product data


General Information			
Light source replaceable	No	Luminous Efficacy (rated) (Nom)	103 lm/W
Number of gear units	1 unit	Color rendering index (CRI)	80
Driver included	Yes	Beam angle of light source	- degree(s)
Light source engine type	LED	Light source color	840 neutral white
Service tag	Yes	Optic type	-
CE mark	CE mark	Optical cover type	Polycarbonate bowl/cover foggy
Warranty period	3 years	Luminaire light beam spread	100°
Flammability mark	-	Operating and Electrical	
ENEC mark	-	Input Voltage	220 to 240 V
Glow-wire test	Temperature 650 °C, duration 5 s	Line Frequency	50 to 60 Hz
EU RoHS compliant	No	Initial CLO power consumption	- W
Light Technical		Average CLO power consumption	- W
Luminous Flux	10,000 lm	Inrush current	10.6 A
Correlated Color Temperature (Nom)	4000 K	Inrush time	0.13 ms
		Power Consumption	97 W

SmartBright Highbay G3

Power Factor (Fraction)	0.9
Connection	-
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	24
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminum die cast
Reflector material	-
Optic material	-
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Dark gray
Optical cover finish	Frosted
Overall height	50 mm
Overall diameter	243 mm
Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38.0.38)SDCM<5
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.01 %
Median useful life L70B50	30,000 hour(s)
Median useful life L80B50	20,000 hour(s)
Median useful life L90B50	10,000 hour(s)
Application Conditions	
Maximum dim level	Not applicable
Product Data	
Order product name	BY239P LED100/NW PSU
Full product name	BY239P LED100/NW PSU
Full product code	911401564751
Order code	911401564751
Material Nr. (12NC)	911401564751
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828633523
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828633622

Dimensional drawing



## SmartBright Highbay G3

